

**DG210 Allcut diamond cutting disc**  
Segment height 3.0 mm

**RHODIUS**

**Application:**

For cool cutting of stone, metal and many other materials. Suitable for wet and dry sanding

**Execution:**

- segmented, soldered under a vacuum
- Reducing rings for bore diameters 20.0 mm and 22.2 mm are included with each 300 mm and 350 mm disc

Art. no.	76119 330
Brand	RHODIUS
Manufacturer Part Number	303391
Washer diameter	230 mm
Washer thickness	2.8 mm
Bore diameter	22.23 mm
Max. rotation speed	6650 rpm
Form	Straight
Number of pieces per packet	1 PCS
Material to be processed	Stone, Concrete, Steel
Gross Weight	0.676 kg
Product Group	6BB

**EAN**

4011890071434

