

Line laser, green, 532 nm, 90 °, 10 mW

LD532-10-24(20x80)-PL-C1500-NT
Order Number: 70124002

Main Parameters (*)	min	typ	max	Unit
Wavelength		532		nm
Optical Output Power		10		mW
Operating Voltage	21.6	24	26.4	V DC
Operating Current	30	50	90	mA
Operating Temperature	15		30	°C
Storage Temperature	-40		80	°C

Main Data

Warranty 1 years

Technical Parameters

Lifetime > 10,000 h
RoHS yes

Optical Parameters

Beam Shape	Line
Laser Class	1
Divergence	D - 0.5 mrad
Fan Angle	90 °
Line Thickness	<1.5mm@3m
Operating Distance	5 m
Optics	glass lens AR coated
Beam Mode	TEM00
Laser technology	Solid State (YVO4+KTP)
Stability	+/- 20% @ 15-30°C
Protection Lens	yes
Focus	fixed (3000mm)
Warm up time	< 15 min

Electrical Parameters

Potential of Housing	isolated
Connector	2.5 mm DC plug (GND pole inner)
Stripping of cable cover	50 mm

Mechanical Parameters

Size	Ø20x80 mm
Material	aluminium
Cable length	1,500 mm
Wire type	22AWG, black, 3,6mm
Output Aperture	5 mm
Housing Color	black
Weight	87 g
Stripping of wire	5 mm

(*) Over the complete operating temperature range



Features

- Operating Voltage 24 V DC
- Isolated housing
- Laser Class 1
- Compact size
- Protection lens


Picture



Cable color

Ground		black	GND
positive		white	21.6 - 26.4, typ 24 V DC

Safety Label



Valid Revision

| 17-DEC-2018