



MINIZED-SWITCH-DISCONNECTOR D01 16A
230/400V 1P+N FOR FUSE-LINKS 2-16A

Figure similar

Model		
product brand name		SENTRON
Product designation		MINIZED fuse switch disconnectors
Design of the product		as draw-out assembly
General technical data		
Number of poles		3
Size of fuse system / acc. to DIN EN 60269-1		D01
Overvoltage category		3
Voltage		
Surge voltage resistance / Rated value	kV	6
Protection class		
Protection class IP		IP20, with connected conductors
Electricity		
Current / with AC / Rated value	A	10
Main circuit		
Operating voltage / with AC / Rated value	V	400
Product details		
Product property / sealable		Yes
Connections		
Tightening torque / with screw-type terminals		
• minimum	N·m	2.5
• maximum	N·m	3

Mechanical Design

Height	mm	70
Width	mm	36
Depth	mm	88
mounting position		any, preferably vertical

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SG76510KK16>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SG76510KK16/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG76510KK16

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015