

Thread go ring gauge

For standard metric ISO thread // improved corrosion resistance

ATORN®

Application

For testing the flank and core diameter of male threads.

Version

- Surface hardness approx. 2500 Vickers

Advantage

- Improved corrosion resistance
- Wear resistance approx. 10 times greater than conventional gauge steel
- Extended calibration intervals
- Cost reduction

Art. No.	32697 060
Calibration Group	AB
Thread type	Metric thread
Thread type x nominal diameter x pitch	M6 x 1.0
Pitch	1 mm
Tolerance class	6g
Material	TiN
DIN	2285-1

EAN-Code

4050293202564

