




**Accessories for actuator/sensor cables**  
**female flange with solder contacts, front-mounted**  
**EC-FSE4-L/16**



- M12 ⌀ 1 male receptacle
- Protection class IP67
- Stainless steel receptacle housing
- Front panel mounting
- Connected via solder contacts

**Pin Assignment**



<b>Type designation</b>	EC-FSE4-L/16
Ident no.	6934066
<b>Connector A side</b>	
Number of pins	Male receptacle, M12 ⌀ 1, Straight 4
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PA GF, Black
Flange housing	Stainless steel, 1.4404 (AISI 316L)
Screw-in thread seal	plastic, NBR
Screw-in thread	M16x1.5
Connection mode	Solder contact
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Protection class	IP67, (screwed together)
<b>Electrical features at +20 °C</b>	
Rated voltage	250 V
Current	4 A
Insulation resistance	≥ 10 <sup>8</sup> Ω
Forward resistance	≤ 5 mΩ
<b>Mechanical and chemical properties</b>	
Ambient temperature	
Stationary	-30...+90°C