




## Precision Thin Film Chip Resistor Array ACAS06S0830372P1AT



### FEATURE

- Product Information

### REFERENCE

This unique special product is derived from the following underlying standard product:

- Precision Thin Film Chip Resistor Array  
ACAS 0612 AT

This document is valid only in conjunction with the underlying standard product's data sheet in its most current edition:

- Precision Thin Film Chip Resistor Array  
Superior Moisture Resistivity  
Document No. 28770

### CHARACTERIZATION

This Unique Special Product is characterized by the following facts:

The product definition meets the ranges published in the referenced data sheet:																																		
<input checked="" type="checkbox"/> COMPLETELY	<input type="checkbox"/> EXCEPT FOR: <table style="margin-left: 20px;"> <tr> <td>Temperature coefficient</td> <td></td> <td></td> </tr> <tr> <td>absolute</td> <td>=</td> <td>± 25ppm/K</td> </tr> <tr> <td>tracking</td> <td>=</td> <td>15ppm/K</td> </tr> <tr> <td>Tolerance on rated resistance</td> <td></td> <td></td> </tr> <tr> <td>absolute</td> <td>=</td> <td>± 0,25%</td> </tr> <tr> <td>matching</td> <td>=</td> <td>0,1%</td> </tr> <tr> <td colspan="3">Rated resistance values</td> </tr> <tr> <td></td> <td>R1 =</td> <td>10 000 Ω</td> </tr> <tr> <td></td> <td>R2 =</td> <td>10 000 Ω</td> </tr> <tr> <td></td> <td>R3 =</td> <td>10 000 Ω</td> </tr> <tr> <td></td> <td>R4 =</td> <td>10 000 Ω</td> </tr> </table>	Temperature coefficient			absolute	=	± 25ppm/K	tracking	=	15ppm/K	Tolerance on rated resistance			absolute	=	± 0,25%	matching	=	0,1%	Rated resistance values				R1 =	10 000 Ω		R2 =	10 000 Ω		R3 =	10 000 Ω		R4 =	10 000 Ω
	Temperature coefficient																																	
	absolute	=	± 25ppm/K																															
	tracking	=	15ppm/K																															
	Tolerance on rated resistance																																	
	absolute	=	± 0,25%																															
matching	=	0,1%																																
Rated resistance values																																		
	R1 =	10 000 Ω																																
	R2 =	10 000 Ω																																
	R3 =	10 000 Ω																																
	R4 =	10 000 Ω																																
Technology and manufacturing are identical to those used for the underlying product:																																		
<input checked="" type="checkbox"/> COMPLETELY	<input type="checkbox"/> EXCEPT FOR: —																																	
The choices of deliverable versions and packaging are identical to those for the underlying product:																																		
<input checked="" type="checkbox"/> COMPLETELY	<input type="checkbox"/> EXCEPT FOR: —																																	
The details published in the referenced data sheet under <table style="width: 100%; border: none;"> <tr> <td style="width: 33%;">• Technical specification</td> <td style="width: 33%;">• Dimensions</td> <td style="width: 33%;">• Description</td> </tr> <tr> <td>• Assembly</td> <td>• Functional performance</td> <td>• Test and Requirements</td> </tr> </table> apply to this product		• Technical specification	• Dimensions	• Description	• Assembly	• Functional performance	• Test and Requirements																											
• Technical specification	• Dimensions	• Description																																
• Assembly	• Functional performance	• Test and Requirements																																
<input checked="" type="checkbox"/> COMPLETELY	<input type="checkbox"/> EXCEPT FOR:																																	

### ORDERING INFORMATION

Product description	ACAS 0612 10K E 10K AT P1
	ACAS 0612 10K E 10K AT P5
Part Number	ACASA1002E1002P5AT
	ACASA1002E1002P1AT