

## Universal chuck

For clamping micro drill bits and milling tools

**ATORN**<sup>®</sup>

### Application

Extremely flexible extension for HYDRO expansion, shrink-fit and collets. For high precision centric clamping of milling, drilling and reaming tools.



### Version

- Speed range up to 60,000 rpm
- Concentricity tolerance < 0.005 mm
- Very wide clamping range
- Chuck with spur gear

<b>Art. No.</b>	<b>23720 315</b>
<b>Min./max. clamping width</b>	0.20-6.4 mm
<b>Shaft diameter</b>	20 mm
<b>Outer diameter</b>	25 mm
<b>Length</b>	200 mm
<b>Length 2</b>	160 mm
<b>Max. length</b>	204 mm
<b>Max. tightening torque</b>	4 Nm
<b>Torque transmission</b>	12 Nm
<b>Concentricity tolerance</b>	0.005 mm
<b>Coolant supply</b>	Internal axial
<b>Balancing quality</b>	G 2.5 at 25 rpm

### EAN-Code

4050293358476