

Vertical clamp

Heavy-duty



Application:

For quick clamping of workpieces.

Version:

- With horizontal base
- Reamed and case-hardened bearing bushes
- Hardened, polished and permanently lubricated studs
- burnished steel, lever arm made of steel casting
- With red oil-resistant plastic handle

Delivery:

With tempered and galvanised thrust bolt



Art. no.	26212 540
Size	4
Hole distance	45 mm
Bore diameter	8.5 mm
Clamping height	44 mm
Retaining force	5 kN
Length, clamped	146 mm
Length, open	160 mm
Thumbscrew size	M12 x 80 mm

EAN-Code

4020772090876