








## Steckzungen 2,8 mm Languettes plates Mounting tabs

					
Artikelnummer Numéro d'article Part-No.	<b>3773e05.2</b> ☒	<b>3775b08.6</b> ☒	<b>03775b08.6</b> ☒	<b>3779wr.2</b> ☒	<b>3779u.2</b> ☒
Bohrung/Trou/Hole	∅ 1.4 T 3.2 L 7 L1 12.3 B1 3.8 B2 2.8 ∅D B 1.5 S 0.5	∅ 1.45 T 7 L 7 L1 16.1 B1 3.9 B2 2.8 ∅D 1.3 B 1.4 S 0.8	∅ 1.45 T 7 L 7 L1 16.1 B1 3.9 B2 2.8 ∅D 1.3 B 1.4 S 0.8	∅ 1.5 T 4.3 L 6.8 L1 12.5 B1 5 B2 2.8 ∅D 1.2 B 1.5 S 0.5	∅ 1.55 T 4.3 L 6.8 L1 12.5 B1 7.2 B2 2.8 ∅D 1.2 B 1.55 S 0.5
Werkzeuge Outils Toolings	<b>17</b>	<b>18</b>	<b>104808</b>	<b>13</b>	<b>17</b>

Werkstoff/Matière/Material  
.2 = Bronze/bronze  
.6 = Messing/laiton/brass








☒ = Oberflächen/Surface/Surface-plating  
Seite/page/page 5.011



### Masse im Steckbereich nach DIN46342, Teil 1

### Dimensions zone d'emboîtement selon DIN46342, partie 1

### Dimensions in the tab sector DIN46342, part 1

							
Artikelnummer Numéro d'article Part-No.	<b>3785s.6</b> ☒	<b>3776b.6</b> ☒	<b>3785y05.6</b> ☒	<b>3785h.6</b> ☒	<b>03785h.6</b> ☒	<b>3785q05.6</b> ☒	<b>03785q05.6</b> ☒
Bohrung/Trou/Hole	∅ 0.8 T 3.5 L 8.1 L1 15.4 B1 8 A 4 ∅D 1.3 B 0.65 S 0.8	∅ 0.9 T 2.5 L 6.5 L1 12.8 B1 4 A 2.5 ∅D 0.9 B 0.9 S 0.5	∅ 0.9 T 2.5 L 10 L1 14.5 B1 5.2 A 2.5 ∅D 1.3 B 0.8 S 0.5	∅ 0.9 T 3.5 L 8.1 L1 15.4 B1 8 A 4 ∅D 1.3 B 0.8 S 0.8	∅ 0.9 T 3.5 L 8.1 L1 15.4 B1 8 A 4 ∅D 1.3 B 0.8 S 0.8	∅ 0.9 T 3.5 L 10 L1 16.9 B1 5.2 A 2.5 ∅D 1.3 B 0.8 S 0.5	∅ 0.9 T 3.5 L 10 L1 16.9 B1 5.2 A 2.5 ∅D 1.3 B 0.8 S 0.5
Werkzeuge Outils Toolings	<b>32</b>	<b>93</b>	<b>64</b>	<b>32</b>	<b>1046h</b>	<b>64</b>	<b>1051q05</b>