


AC6001

IO-Link master with AS-i interface

IO-Link Master AS-i 4P IP69K



CE

Application

| | |
|----------------------|------------------------------------------------------|
| Application | hygienic systems; I/O modules for field applications |
| Daisy-chain function | voltage supply; fieldbus interface |

Electrical data

| | | |
|------------------------------------|------|-----------------------------------------------------|
| Operating voltage | [V] | 18...31.6 DC; (AS-i) |
| Current consumption | [mA] | 300...1500; (AUX) |
| Max. current consumption from AS-i | [mA] | 100 |
| Protection class | | III |
| Max. current load total | [A] | 1.1; (ports 1+2: 0.55 (AUX); ports 3+4: 0.55 (AUX)) |
| Additional voltage supply | [V] | 20...30 DC; (AUX) |

Inputs / outputs

| | |
|------------------------------------|-----------------------------------------------------------|
| Total number of inputs and outputs | 8; (configurable) |
| Number of inputs and outputs | Number of digital inputs: 8; Number of digital outputs: 4 |

AC6001



IO-Link master with AS-i interface

IO-Link Master AS-i 4P IP69K

| Inputs | | | |
|-------------------------------------------------|---------|---------------------------------------------------------------------------------------|-------------|
| Number of digital inputs | | 8; (IO-Link Port Class A: 4 x 2) | |
| Sensor supply of the inputs | | AUX | |
| Switching level high [V] | | 11...30 | |
| Switching level low [V] | | 0...5 | |
| Digital inputs protected against short circuits | | yes | |
| Outputs | | | |
| Number of digital outputs | | 4; (IO-Link Port Class A: 4 x 1) | |
| Max. current load per output [mA] | | 300 | |
| Short-circuit proof | | yes | |
| Actuator supply switching outputs | | AUX | |
| Interfaces | | | |
| Communication interface | | IO-Link; AS-i | |
| IO-Link Master | | | |
| Transmission type | | COM 1 / COM 2 / COM 3 | |
| IO-Link revision | | 1.1 | |
| Number of ports class A | | 4 | |
| Operating conditions | | | |
| Ambient temperature [°C] | | -25...60 | |
| Storage temperature [°C] | | -25...85 | |
| Max. relative air humidity [%] | | 90 | |
| Protection | | IP 65; IP 66; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K) | |
| Degree of soiling | | 2 | |
| Tests / approvals | | | |
| EMC | | EN 61000-6-2 EN 61000-6-4 | |
| Shock resistance | | DIN EN 60068-2-27 | |
| Vibration resistance | | DIN EN 60068-2-64 2009-04 DIN EN 60068-2-6 2008-10 | |
| AS-i classification | | | |
| AS-i version | | 2.11; 3.0 | |
| Extended addressing mode possible | | no | |
| AS-i profile | | S-7.4.E; (CTT1 input) | |
| Number of AS-i devices | | 1...5 | |
| Further AS-i profiles | S-7.3.E | : | CTT1 input |
| | S-7.3.2 | : | CTT1 output |
| Mechanical data | | | |
| Weight [g] | | 255 | |
| Materials | | housing: PA grey; socket: stainless steel (1.4404 / 316L) | |
| Remarks | | | |
| Remarks | | For further information please see the operating instructions. | |
| Pack quantity | | 1 pcs. | |

AC6001



IO-Link master with AS-i interface


IO-Link Master AS-i 4P IP69K

Electrical connection - Process connection

IO-Link Port Class A X01...X04

- | | |
|---|-----------------|
| 1 | + 24 V DC (AUX) |
| 2 | digital input |
| 3 | GND (AUX) |
| 4 | C/Q IO-Link |
| 5 | not used |

Connector: 4 x M12




Electrical connection - voltage supply IN

X21

- | | |
|---|--------|
| 1 | AS-i + |
| 2 | AUX - |
| 3 | AS-i - |
| 4 | AUX + |

Connector: 1 x M12



Electrical connection - voltage supply OUT

X22

- | | |
|---|----------|
| 1 | AS-i + |
| 2 | AUX - |
| 3 | AS-i - |
| 4 | AUX + |
| 5 | not used |

Connector: 1 x M12

AC6001



IO-Link master with AS-i interface

IO-Link Master AS-i 4P IP69K

