


www.vishay.com

Vishay Semiconductors

High Efficiency LED in Ø 3 mm Clear Package



DESCRIPTION

The TLH.4900 series was developed for applications where high light output is required.

It is housed in a 3 mm clear plastic package. The small viewing angle of these devices provides a high brightness.

All LEDs are categorized in luminous intensity groups. The green and yellow LEDs are categorized additionally in wavelength groups.

That allows users to assemble LEDs with uniform appearance.

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: 3 mm
- · Product series: standard
- Angle of half intensity: ± 16°

FEATURES

- Choice of four bright colors
- Standard Ø 3 mm (T-1) package
- Small mechanical tolerances
- Suitable for DC and high peak current
- Very small viewing angle
- Luminous intensity categorized
- Yellow and green color categorized
- Material categorization: for definitions of [5-2008] compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Status lights
- Off / on indicator
- Background illumination
- Readout lights
- Maintenance lights
- Legend light

PARTS TABLE														
PART	T COLOR		LUMINOUS INTENSITY (mcd)		at I _F				at I _F (mA)	FORWARD VOLTAGE (V)		at I _F (mA)	TECHNOLOGY	
		MIN.	TYP.	MAX.	(mA)	MIN.	TYP.	MAX.	(IIIA)	MIN.	TYP.	MAX.	(IIIA)	
TLHR4900	Red	6.3	25	-	10	612	-	625	10	-	2	3	20	GaAsP on GaP
TLHY4900	Yellow	10	26	-	10	581	-	594	10	-	2.4	3	20	GaAsP on GaP
TLHG4900	Green	16	37	-	10	562	-	575	10	-	2.4	3	20	GaP on GaP
TLHG4900-AS12Z	Green	16	37	-	10	562	-	575	10	-	2.4	3	20	GaP on GaP

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified) **TLHG4900, TLHR4900, TLHY4900**

1LNG4900, 1LNN4900, 1LN14900							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
Reverse voltage		V _R	6	V			
DC forward current	T _{amb} ≤ 60 °C	I _F	30	mA			
Surge forward current	t _p ≤ 10 μs	I _{FSM}	1	А			
Power dissipation	T _{amb} ≤ 60 °C	Pv	100	mW			
Junction temperature		Тj	100	°C			
Operating temperature range		T _{amb}	-40 to +100	°C			
Storage temperature range		T _{stg}	-55 to +100	°C			
Soldering temperature	$t \le 5$ s, 2 mm from body	T _{sd}	260	°C			
Thermal resistance junction/ambient		R _{thJA}	400	K/W			





www.vishay.com

Vishay Semiconductors

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified) TLHR4900, RED							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Luminous intensity (1)	I _F = 10 mA	I _V	6.3	25	-	mcd	
Dominant wavelength	I _F = 10 mA	λ _d	612	-	625	nm	
Peak wavelength	I _F = 10 mA	λρ	-	635	-	nm	
Angle of half intensity	I _F = 10 mA	φ	-	± 16	-	deg	
Forward voltage	I _F = 20 mA	V _F	-	2	3	V	
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V	
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	50	-	pF	

Note

(1) In one packing unit $I_{Vmin}/I_{Vmax} \le 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified) **TLHY4900, YELLOW**

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity (1)	I _F = 10 mA	Ι _V	10	26	-	mcd
Dominant wavelength	I _F = 10 mA	λ _d	581	-	594	nm
Peak wavelength	I _F = 10 mA	λρ	-	585	-	nm
Angle of half intensity	I _F = 10 mA	φ	-	± 16	-	deg
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	50	-	pF

Note

(1) In one packing unit $I_{Vmin}/I_{Vmax} \le 0.5$

OPTICAL AND ELECTRICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified) TLHG4900. GREEN

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity ⁽¹⁾	I _F = 10 mA	IV	16	37	-	mcd
Dominant wavelength	I _F = 10 mA	λ _d	562	-	575	nm
Peak wavelength	I _F = 10 mA	λρ	-	565	-	nm
Angle of half intensity	I _F = 10 mA	φ	-	± 16	-	deg
Forward voltage	I _F = 20 mA	V _F	-	2.4	3	V
Reverse voltage	I _R = 10 μA	V _R	6	15	-	V
Junction capacitance	V _R = 0 V, f = 1 MHz	Cj	-	50	-	pF

Note

⁽¹⁾ In one packing unit $I_{Vmin}/I_{Vmax} \le 0.5$

LUMINOUS INTENSITY CLASSIFICATION							
GROUP	LUMINOUS INTENSITY (mcd)						
GROUP	MIN.	MAX.					
Q	6.3	12.5					
R	10	20					
S	16	32					
Т	25	50					
U	40	80					
V	63	125					

Note

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel or bulk (there will be no mixing of two groups on one reel/bulk). In order to ensure availability, single brightness groups will not be orderable. In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one reel/bulk. In order to ensure availability, single wavelength groups will not be orderable.

	DOM. WAVELENGTH (nm)						
GROUP	YEL	LOW	GR	EEN			
	MIN.	MAX.	MIN.	MAX.			
0							
1	581	584					
2	583	586					
3	585	588	562	565			
4	587	590	564	567			
5	589	592	566	569			
6	591	594	568	571			
7			570	573			
8			572	575			

• Wavelengths are tested at a current pulse duration of 25 ms.



TLHG4900, TLHR4900, TLHY4900

Vishay Semiconductors

TYPICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 2 - Forward Current vs. Pulse Length




Fig. 3 - Relative Luminous Intensity vs. Angular Displacement




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 6 - Relative Luminous Intensity vs. Forward Current/Duty Cycle

3

For technical questions, contact: <u>LED@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors




Fig. 7 - Relative Luminous Intensity vs. Forward Current




Fig. 8 - Relative Intensity vs. Wavelength




Fig. 9 - Forward Current vs. Forward Voltage





Fig. 10 - Relative Luminous Intensity vs. Ambient Temperature






Fig. 12 - Relative Luminous Intensity vs. Forward Current

Rev. 2.4, 24-Mar-15

4

Document Number: 83009

For technical questions, contact: LED@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay Semiconductors




Fig. 13 - Relative Intensity vs. Wavelength




Fig. 14 - Forward Current vs. Forward Voltage




Fig. 15 - Rel. Luminous Intensity vs. Ambient Temperature




Fig. 16 - Specific Luminous Intensity vs. Forward Current




Fig. 17 - Relative Luminous Intensity vs. Forward Current




Fig. 18 - Relative Intensity vs. Wavelength

Rev. 2.4, 24-Mar-15

5 For technical questions, contact: <u>LED@vishav.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





TLHG4900, TLHR4900, TLHY4900

Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters









technical drawings according to DIN specifications

Drawing-No.: 6.544-5255.02-4 Issue: 5; 28.07.14

TAPE





Fig. 19 - LED in Tape

АММОРАСК



Note

 The new nomenclature for ammopack is e.g. ASZ only, without suffix for the LED orientation. The carton box has to be turned to the desired position: "+" for anode first, or "-" for cathode first. AS12Z and AS21Z are still valid for already existing types, BUT NOT FOR NEW DESIGN.


6 For technical questions, contact: <u>LED@vishay.com</u>



Vishay Semiconductors

TAPE DIMENSIONS in millimeters

94 8171



Option	Dim. "H" ± 0.5 mm
AS	17.3

2000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.