


IE5328



Inductive sensor

IEB3002BBPKG/AS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Application

Special feature	Increased sensing range
-----------------	-------------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Short-time current rating of switching output [mA]	200
Switching frequency DC [Hz]	1300
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	2
Operating distance [mm]	0...1.62
Increased sensing range	yes

Accuracy / deviations


Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...20

IE5328



Inductive sensor

IEB3002BBPKG/AS

Operating conditions		
Ambient temperature	[°C]	0...70
Protection		IP 65; (with ifm socket duly screwed on; "Coolant": IP67)
Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	2378
UL approval	Ta	0...70 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	File number UL	E174191
Mechanical data		
Weight	[g]	18.9
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Materials		brass white bronze coated; LCP
Displays / operating elements		
Display	switching status	4 x 90° LED, yellow
Accessories		
Accessories (supplied)		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M8		
		



IE5328



Inductive sensor

IEB3002BBPKG/AS

Connection

