# multicomp PRO

#### Features

- · Applicable to both standard loads and microload
- Conforms to EN115 and EN81-1
- Certified standards: UL, EN(TUV), and CCC

#### Characteristics

	IP67			
Rating	IEC 60947-5-1	AC-15 240V AC / 3A, DC-13 250V DC / 0.27A		
-	UL508	A300 250VAC / 15A		
	Mechanical	15,000,000 operations min.		
Durability	Electrical	500,000 operations min. (3A resistive load at 250V AC) 300,000 operations min. (10A resistive load at 250V AC)		
	1 to 500 mm/s			
Operating Frequency	Mechanical	- 30 operations / minute max.		
	Electrical			
	50/60Hz			
	100MΩ min.			
	25mΩ max.			
Dielectric Strength	Between terminals of same polarity	2.5kV		
	Between current-carrying metal parts and ground	4kV		
	Between each terminal and non-current-carrying metal part	6kV		
	300V			
P	ollution degree (Application environment)	3 (EN60947-5-1)		
	Conditional short-circuit current	100A (EN60947-5-1)		
	10A (EN60947-5-1)			
D	Class II			
Vibration Resistance	Malfunction	10~55 Hz 0.75mm single amplitude		
Oha als Da aistar	Destruction	1,000m/s² min.		
Shock Resistance	Malfunction	300m/s² min.		
	-30°C ~ +70°C with no icing			
	95% RH			

#### Notes:

- 1. Above values of these characteristics are initial values.
- 2. Above values of these characteristics may are depending on different models.
- 3. Above durability is for an ambient temperature of 5 to 35° and ambient humidity of 40% to 70%.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




#### **Operating Characteristics**

Part Number	Operating Force (Max.)	Release Force (Min.)	Pre Travel (Max.)	Over Travel (Min.)	Movement Differential (Max.)	Operating Position	Total Travel	Direct Opening Travel	Direct Opening Force
MC002449	6.5N	1.5N	2mm	4mm	1mm	18.2 ±0.5mm	(6mm)	3.2mm	20N
MC002450	6.5N	1.5N	2mm	4mm	1mm	28.6 ±0.8mm	(6mm)	3.2mm	20N
MC002451	5N	0.5N	18 ~ 27°	40°	14°	-	(80°)	50°	20N
MC002452	4.5N	0.4N	18 ~ 27°	40°	14°	-	(80°)	50°	20N
MC002453	4.5N	0.4N	18 ~ 27°	40°	14°	-	(80°)	50°	20N
MC002454	5N	0.8N	4mm	5mm	1.5mm	37 ±0.8mm	(9mm)	5.8mm	20N
MC002455	1.5N	-	15°	-	-	-	-	-	-

#### Standard Top Plunger






MC002449

Weight: 56.3g

#### Vertical Standard Roller Lever







MC002451 Weight: 84.1g

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

### **Standard Roller Plunger**








MC002450

Weight: 63.1g

#### Adjustable Roller Lever, Form Lock (With Metal Lever, rubber Roller)




Dimensions : Millimetres



## multicomp PRO


### Adjustable Roller Lever, Form Lock (with Metal Lever, Rubber Roller)





MC002453 Weight: 100.7g

**Cat Whisker** 



MC002455 Weight: 71g

#### Part Number Table


#### Part Number Description Vertical Limit Switch, Miniature Safety, Standard Top Plunger, Screw Terminal MC002449 Vertical Limit Switch, Miniature Safety, Standard Roller Plunger, Screw Terminal MC002450 Vertical Limit Switch, Miniature Safety, Vertical Standard Roller Lever, Screw Terminal MC002451 Vertical Limit Switch, Miniature Safety, Adjustable Roller Lever, Form Lock, Screw Terminal MC002452 Vertical Limit Switch, Miniature Safety, Adjustable Roller Lever, Form Lock, Screw Terminal MC002453 Vertical Limit Switch, Miniature Safety, One-Way Roller Arm Lever (Horizontal), Screw Terminal MC002454 Vertical Limit Switch, Miniature Safety, Cat Whisker, Screw Terminal MC002455

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet on the Information on and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



### One-way Roller Arm Lever (Horizontal)



Weight: 64g

Dimensions : Millimetres

, , oigint, 7 19