Product data sheet Characteristics

RPF2AP7

Power plug-in relay, 30 A, 2 NO, 230 V AC





Main

Range of product	Harmony Relay
Series name	Power
Product or component type	Plug-in relay
Device short name	RPF
Contacts type and composition	2 NO
[Uc] control circuit voltage	230 V AC
Control type	Without lockable test button
Shape of pin	Flat
Contacts material	Silver tin oxide
[Ithe] conventional enclosed thermal current	25 A -40131 °F (-4055 °C) relays side by side without a gap 30 A -40131 °F (-4055 °C) 13 mm gap between two relays
Resistive rated load	25 A 28 V DC 30 A 250 V AC
Utilisation coefficient	10 %


Complementary

Panel DIN rail
184253 V
30 A 277 V AC) NO UL 20 A 28 V DC) NO UL 30 A 250 V AC) NO IEC 25 A 28 V DC) NO IEC
250 V conforming to IEC 300 V UL
4 kV 1.2/50 μs
250 V IEC
7500 VA/700 W
6000 mW 500 mA / 12 V NO
<= 1200 cycles/hour under load <= 18000 cycles/hour no-load
5000000 cycles
100000 cycles for resistive load
4 VA 60 Hz
>= 0.15 Uc
25 ms
25 ms
15600 Ohm 68 °F (20 °C) +/- 15 %
B10d = 100000
RT II
Level A group mounting
Any position
1.33 in (33.7 mm)
2.70 in (68.5 mm)
1.54 in (39.2 mm)

Net Weight	0.18 lb(US) (0.082 kg)
Device presentation	Complete product
Environment	
Dielectric strength	2000 V AC between poles basic
2.0.00.0.0 0.0.0 ga.	4000 V AC between coil and contact reinforced 1500 V AC between contacts micro disconnection
Standards	CSA C22.2 No 14 EN/IEC 61810-1 UL 508
Product certifications	CSA CE GOST UL
Ambient air temperature for storage	-40185 °F (-4085 °C)
Ambient air temperature for operation	-4055 °C
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 10 gn +/- 1 mm 10150 Hz)5 cycles not operating
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	10 gnin operation 30 gnnot operating
Pollution degree	3
Ondoring and chinates (ICC)	
Ordering and shipping details Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	00785901526018
Nbr. of units in pkg.	10
Package weight(Lbs)	0.18 lb(US) (0.08 kg)
Returnability Country of origin	Yes CN
ocalia, c. o.igii.	
Packing Units Package 1 Height	0.420 dm
Package 1 width	0.350 dm
Package 1 Length	0.690 dm
Offer Sustainability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₽¥Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Contractual warranty	
Contractual warranty Warranty	18 months


RPF2AP7

Dimensions



RPF2AP7


Wiring Diagram



Symbols shown in blue correspond to Nema marking.

Electrical Durability of Contacts

AC Resistive load




X Switching capacity (kVA)

Y Durability (number of operating cycles)


AC Reduction coefficient for inductive load (depending on power factor cos φ)

Durability (inductive load) = durability (resistive load) x reduction coefficient.



Y reduction coefficient

Maximum switching capacity on DC resistive load



A 30 A B 25 A

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.