# ATyS S - ATyS d S

# Remotely operated Transfer Switching Equipment from 40 to 125 A



## **Function**

**ATyS S** products are 4 pole remotely operated transfer switches with positive break indication. They enable the on-load transfer of two three-phase supplies via remote volt-free contacts, from either an external automatic controller, using pulse logic, or a switch.

They are intended for use in low voltage power supply systems where a brief interruption of the load supply is acceptable during transfer.

# Advantages

### Extensive power supply range

The ATyS S is available in four supply versions, each with a broad range (+/-30%).

The four versions are:

- 12 VDC power supply.
- 24/48 VDC power supply.
- 230 VAC single power supply.
- 2 x 230 VAC dual power supply.

# Safety and reliability

ATyS S products use stable position technology, ensuring constant pressure on the contacts and preventing premature faults. In addition, they do not require a power supply to maintain position, thus protecting their loads from voltage fluctuations.

# Easy integration

ATyS S products can be easily installed inside enclosures. Their design, and in particular their compact size, enables integration within most 200 mm deep enclosures.

### Simplified maintenance

Maintenance can be carried out easily under load, with manual operation still available.

The control and motorisation section can be replaced simply by removing 4 screws, with no work required on the installation cabling.

### ATyS d S: Dual power supply

In addition to the functions offered by the ATyS S, the ATyS d S incorporates supply redundancy without the need for additional wiring. This is obtained by integrating a double supply (2 independent supplies) directly within the product.

# The solution for

- > Genset < 90 kVA
- > Heating systems
- > Climate control
- > Ventilation systems
- > Telecommunications



# Strong points

- Extensive power supply range
- > Safety and reliability
- > Easy integration
- > Simplified maintenance
- > ATyS d S: Dual power supply

## **Conformity to standards**

- > IEC 60947-6-1
- > IEC 60947-3
- > GB/T 14048-11



# **Approvals and certifications**



## **Enclosed ATyS S**





# References

# ATyS S

Rating (A)	No. of poles	Power supply	ATyS S	Bridging bars	Terminal shrouds	Voltage tap	Terminal retainer	DIN rail
	4 P	24/48 VDC	9506 <b>4004</b>		Source side 2 pieces 9594 <b>4012</b> Load side 2 pieces 9594 <b>9012</b>			4 modules 9599 <b>4002</b>
40 A	4 P	12 VDC	9505 <b>4004</b>					
	4 P	230 VAC	9503 <b>4004</b>			9599 <b>4001</b>		
	4 P	24/48 VDC	9506 <b>4006</b>					
63 A	4 P	12 VDC	9505 <b>4006</b>				2 pieces 9599 <b>4003</b>	
	4 P	230 VAC	9503 <b>4006</b>			9599 <b>4001</b>		
	4 P	24/48 VDC	9506 <b>4008</b>					
80 A	4 P	12 VDC	9505 <b>4008</b>	4 P 9509 <b>4013</b>				
	4 P	230 VAC	9503 <b>4008</b>			9599 <b>4001</b>		
	4 P	24/48 VDC	9506 <b>4010</b>					
100 A	4 P	12 VDC	9505 <b>4010</b>					
	4 P	230 VAC	9503 <b>4010</b>			9599 <b>4001</b>		
	4 P	24/48 VDC	9506 <b>4012</b>					
125 A	4 P	12 VDC	9505 <b>4012</b>					
	4 P	230 VAC	9503 <b>4012</b>			9599 <b>4001</b>		

# ATyS d S

Rating (A)	No. of poles	Power supply	ATyS d S	Bridging bars	Terminal shrouds	Voltage tap	Terminal retainer	DIN rail
40 A	4 P	2 x 230 VAC	9513 <b>4004</b>		Source side			
63 A	4 P	2 x 230 VAC	9513 <b>4006</b>		2 pieces 9594 <b>4012</b>			
80 A	4 P	2 x 230 VAC	9513 <b>4008</b>	4 P 9509 <b>4013</b>		9599 <b>4001</b>	2 pieces 9599 <b>4003</b>	4 modules 9599 <b>4002</b>
100 A	4 P	2 x 230 VAC	9513 <b>4010</b>	3303 4010	Load side 2 pieces		3333 4300	3333 <b>4332</b>
125 A	4 P	2 x 230 VAC	9513 <b>4012</b>		9594 <b>9012</b>			

# Accessories

# Bridging bars

## Use

For bridging power terminals on the top or bottom side of the switch.

Rating (A)	No. of poles	Reference	
40 125	4 P	9509 <b>4013</b>	



# Voltage tap

## Use

Enables the required power supply for ATyS S 230 VAC and ATyS d S products to be tapped directly from the product's incoming power terminals. Can also be utilised in applications without neutral, to provide 400 VAC to the autotransformer.

Rating (A)	Reference
40 125	9599 <b>4001</b>



# Terminal retainer

# Use

These clips have a dual function: - to prevent direct access to the power supply and control terminals and

- to secure these connector terminals.

Rating (A)	Pack	Reference	
40 125	2 pieces	9599 <b>4003</b>	





# ATyS S - ATyS d S Remotely operated Transfer Switching Equipment

from 40 to 125 A

# Accessories (continued)

# Terminal shrouds

IP2X protection against direct contact with terminals or connecting parts.

Terminal shrouds for the source side						
Rating (A)	Pack	Reference				
40 125	2 pieces	9594 <b>4012</b>				
Terminal shrouds for the loa	ad side					
Rating (A)	Pack	Reference				
40 125	2 pieces	9594 <b>9012</b>				



# Autotransformer 400/230 VAC

# Use

For applications without neutral, this autotransformer provides the 230 VAC required to power these ATyS products.

#### **Dimensions**

75 x 80 x 72 mm

Rating (A)	Reference
40 125	9599 <b>4004</b>

# DIN rail

This 4-module DIN rail can be installed directly on the front of the ATyS S and can be utilised, for example, for the installation of a surge protection device.

Rating (A)	Reference
40 125	9599 <b>4002</b>



# Spares

# Manual emergency operation handle

This handle can be used on the product whether the motor unit is mounted or not.

Rating (A)	Reference
40 125	9599 <b>5012</b>



# Connector kit

This kit, including all the connector types for the different products, can be ordered in case of loss or breaking of one connector.

Rating (A)	Reference
40 125	9509 <b>0002</b>



# Characteristics according to IEC 60947-3 and IEC 60947-6-1

# 40 to 125 A

Thermal current I <sub>th</sub> at 40°C		40 A	63 A	80 A	100 A	125 A
Rated insulation voltage U <sub>i</sub> (V) (power	circuit)	800	800	800	800	800
Rated impulse withstand voltage Uimi		6	6	6	6	6
Rated insulation voltage U <sub>i</sub> (V) (control		300	300	300	300	300
Rated impulse withstand voltage Uimp	,	4	4	4	4	4
Pated operational currents I. (/	) according to IEC 60047-6-1					
Rated operational currents I <sub>e</sub> (A	i -	A /D	A/D	A /D	A /D	A /D
Rated voltage 415 VAC	Utilisation category AC-31 B	<b>A/B</b> 40	<b>A/B</b> 63	<b>A/B</b> 80	<b>A/B</b> 100	<b>A/B</b> 125
415 VAC	AC-31 B	40	63	80	80	80
413 VAO	AO-32 D	40	03	80	00	80
Rated operational currents I <sub>e</sub> (A	A) according to IEC 60947-3					
Rated voltage	Utilisation category	A/B	A/B	A/B	A/B	A/B
415 VAC	AC-20 A / AC-20 B	40/40	63/63	80/80	100/100	125/125
415 VAC	AC-21 A / AC-21 B	40/40	63/63	80/80	100/100	100/125
415 VAC	AC-22 A / AC-22 B	40/40	63/63	80/80	100/100	100/100
415 VAC	AC-23 A / AC-23 B	-/40	-/63	-/63	-/63	-/63
Fuse protected short-circuit wi	thetand (kA rms prospective)					
		50	F0	50	05	15
Prospective short-circuit current (kA	misj	50 40	50 63	50 80	25 100	15 125
Associated fuse rating (A)		40	03	60	100	120
Circuit breaker protected short	-circuit withstand with any circ	uit breaker that	ensures tripping	in less than 0.3s	S <sup>(3)</sup>	
Rated short-time withstand current 0	.3s I <sub>cw</sub> (kA rms)	3.5	3.5	3.5	3.5	3.5
				'		•
Short-circuit capacity as per IE	C 60947-6-1					
Rated short-time withstand current 0	.03 s. (kA)	5	5	5	5	-
Rated short-circuit making capacity l	<sub>cm</sub> (kA peak)	7.65	7.65	7.65	7.65	-
Short-circuit capacity as per IE	C 60947-3 (without protection)	1				
Rated short-time withstand current 1		2.5	2.5	2.5	2.5	2.5
Rated peak withstand current (kA pe	. , ,	12	12	12	12	12
riated poart without and carron (it the	ary	12	12	12	12	12
Connection						
Maximum Cu cable cross-section (m	m²)	50	50	50	50	50
Tightening torque mini / maxi (Nm)		1.2/3	1.2/3	1.2/3	1.2/3	1.2/3
Cusitable at time (Ctandord catti	1					
Switching time (Standard setting	19)	500		500		500
I - 0 or II - 0 (ms)		500	500	500	500	500
I - II or II - I (ms)  Duration of "electrical blackout" I - II (	in a) mainting up	1000 500	1000	1000	1000 500	1000 500
Duration of electrical blackout 1 - II (	rns) minimum	500	500	500	500	500
Power supply						
Power supply 12 VDC min / max (VD	C)	9/15	9/15	9/15	9/15	9/15
Power supply 24/48 VDC min / max		17/62	17/62	17/62	17/62	17/62
Power supply 230 VAC min / max (Va	AC)	160/310	160/310	160/310	160/310	160/310
0 1 1 1						
Control supply power demand		I				
Power supply 12 VDC inrush / nomin	,	200/40	200/40	200/40	200/40	200/40
Power supply 24/48 VDC inrush / no	\ /	200/40	200/40	200/40	200/40	200/40
Supply 230 VAC inrush / nominal (VA	N)	200/40	200/40	200/40	200/40	200/40
Mechanical characteristics						
Durability (number of operating cycles	s)	25 000	25 000	25 000	25 000	25 000
Weight ATyS S and ATyS d S 4 P (kg	,	3	3	3	3	3
, , , , , , , , , , , , , , , , , , , ,						

<sup>(1)</sup> Value for coordination with any circuit breaker that ensures tripping in less than 0.3s. For coordination with specific circuit-breaker references, higher short-circuit current values are available. Please consult us.




# ATyS S - ATyS d S

# Remotely operated Transfer Switching Equipment

from 40 to 125 A


# Terminals and connections

# ATyS S DC version




- 1 preferred source
- 2 alternate source
- 1: position 0 control
- 2: position I control
- 3: position II control
- 4: auxiliary contact, closed when the switch is in position 0
- 5: auxiliary contact, closed when the switch is in position II
- 6: auxiliary contact, closed when the switch is in position I
- 7: power supply 12 VDC (9-15 VDC) or 24 VDC / 48 VDC (17-62 VDC) depending on the version.

# ATyS S: 230 VAC



- 1 preferred source 2 alternate source
- 1: position 0 control
- 2: position I control
- 3: position II control
- 4: auxiliary contact, closed when the switch is in position 0
- 5: auxiliary contact, closed when the switch is in position II
- 6: auxiliary contact, closed when the switch is in position I
- 7: power supply kit: 230 VAC (160-310 VAC)


# ATyS d S: 2 x 230 VAC



- 1 preferred source
- 2 alternate source
- 1: position 0 control
- 2: position I control
- 3: position II control
- 4: auxiliary contact, closed when the switch is in position 0
- 5: auxiliary contact, closed when the switch is in position II
- 6: auxiliary contact, closed when the switch is in
- 7: power supply kit I: 230 VAC (160-310 VAC)
- 8 : power supply kit II: 230 VAC (160-310 VAC)



# **Dimensions**



# Connection terminal

