


## Screw tap, HSSE PG ISO 2 (6H) 0° 40432 C

for universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>

### Application

For producing armoured pipe threads (PG) on CNC or conventional machines in **through holes** in the steel (stainless steel), non-ferrous metals and (cast iron) material groups up to a strength of 1000 N/mm<sup>2</sup>.



### Version

- with over-long shank

### Advantage

- good service life and process reliability thanks to innovative cutting geometry and universal use for the greatest flexibility in applications

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	16	12		9		18	18	15	18	15	15	13		16					

<b>Art. No.</b>	<b>13228 160</b>
<b>Type</b>	P MAX 1000 Control
<b>Thread type</b>	PG
<b>Thread type x nominal diameter in inches</b>	PG 16 in
<b>Number of thread starts per inch</b>	18
<b>Hole type</b>	Clearance hole ≤ 3xD
<b>Cutting material</b>	HSS
<b>Surface</b>	Uncoated
<b>Lead angle shape</b>	C
<b>Tolerance of screw taps</b>	ISO 2 (6H)
<b>Twist angle</b>	0°
<b>Shaft diameter</b>	18 mm
<b>Application type/machine type</b>	CNC, Conventional
<b>Core hole diameter</b>	21.25 mm
<b>Coolant supply</b>	External
<b>Length</b>	80 mm
<b>Shank square</b>	14.5 mm
<b>Cutting speed (steel 1000) suitability</b>	1
<b>Cutting speed (steel 1300) suitability</b>	3
<b>Overall stainless steel suitability</b>	3
<b>fitness not iron total</b>	1
<b>fitness Titan/Nickel/Super total</b>	3
<b>Cutting speed (cast) suitability</b>	2
<b>Cutting speed (hard 55) suitability</b>	3
<b>Cutting speed (hard 65) suitability</b>	3
<b>DIN</b>	40432

### EAN-Code

4050293189292