



PLUG-IN RELAY 4 CHANGEOVER CONT.,W/O TEST BR. 24V DC

Figure similar

**General technical data:**

Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> <li>• for DC Rated value</li> <li>— minimum</li> <li>— maximum</li> </ul>	V	24
	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		4
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> <li>• at DC-13</li> <li>— at 24 V</li> <li>• at AC-15</li> <li>— at 230 V</li> </ul>	A	6
	A	4
Design of the switching function positively driven		No
Switching behavior		monostable

**Mechanical data:**

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		No
Width	mm	22.5
Height	mm	28
Depth	mm	35

**Certificates/ approvals:**



[Declaration of  
Conformity](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZX:PT520024>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:PT520024>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=LZX:PT520024&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZX:PT520024&lang=en)

last modified:

15.01.2015