

## MULTIPAL large-compartment rack

Galvanised, with steel panels



### Execution:

- Large compartment shelf with steel panels for the storage of light to medium-heavy individually packaged items, not suitable for the storage of pallets
- Basic rack, can be expanded as required using an add-on rack
- 4 hook-clasps in 50 mm grid height-adjustable
- Closed box-type profiles ensure high stability
- Rack type 85/20: Flat pack design, comprising cold-formed profiles, bolted to the structure with the infill
- Planning dimensions basic shelf: Total width = strut length + 170 mm, total depth = frame depth, planning dimension add-on shelf: Total width = strut length + 85 mm, total depth = frame depth
- Safety precaution: The loads indicated per shelf and per bay apply to uniformly distributed loads with at least 4 shelf bays and 2 strut pairs. Please note: Steel panel shelves are not suitable for storing pallets.
- Colour: Galvanised rack, in RAL 5010 gentian blue upon request, struts in RAL 2001 red-orange

### Delivery:

Including floor anchor



|  |  |
|--|--|
| <b>Art. no.</b>                              | <b>50171 008</b>   |
| <b>Brand</b>                                 | META   |
| <b>Manufacturer Part Number</b>              | 200188547  |
| <b>Height</b>                                | 2700 mm  |
| <b>Depth</b>                                 | 800 mm   |
| <b>Nominal length</b>                        | 1825 mm  |
| <b>Type of shelving</b>                      | Shelving unit  |
| <b>Design</b>                                | With steel panel   |
| <b>Type of assembly</b>                      | Screw mounting   |
| <b>Surface</b>                               | Zinc plated  |
| <b>ESD-capable</b>                           | No   |
| <b>Design of the frame</b>                   | Disassembled   |
| <b>Grid dimension</b>                        | 50 mm  |
| <b>Number of shelves</b>                     | 4 PCS  |
| <b>Load-carrying capacity per shelf</b>      | 1800 kg  |
| <b>Load-carrying capacity per field</b>      | 10000 kg   |
| <b>Number of frame</b>                       | 2 PCS  |
| <b>Quality label</b>                         | RAL-RG 614/2   |
| <b>Made in</b>                               | Germany  |
| <b>Product certification</b>                 | Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund)                |
| <b>Approval mark</b>                         | GS - MPA NRW   |
| <b>Approval mark - Product certification</b> | GS - MPA NRW - Institute for Materials Research and Testing (MPA) North Rine Westphalia (NRW) (Dortmund) |
| <b>Gross Weight</b>                          | 170.072 kg   |
| <b>Product Group</b>                         | 508  |

### EAN

4026212342512