


# DIN 935-1

## Sechskant-Kronenmuttern



≤ M 10 ≥ M 12

Maße	M 4	M 5	M 6	M 8	M 10	M 12	M 14	M 16
$d_{e \text{ max.}}$	-	-	-	-	-	16	18	22
m	5	6	7,5	9,5	12	15	16	19
$n_{\text{min.}}$	1,2	1,4	2	2,5	2,8	3,5	3,5	4,5
$s_{\text{ISO/DIN}}$	7	8	10	13	16/17	18/19	21/22	24
$w_{\text{max.}}$	3,2	4	5	6,5	8	10	11	13
Splint	1x10	1,2x12	1,6x14	2x16	2,5x20	3,2x22	3,2x25	4x28

Maße	M 18	M 20	M 22	M 24	M 27	M 28*	M 30	M 32*
$d_{e \text{ max.}}$	25	28	32	34	38	38	42	46
m	21	22	26	27	30	30	33	35
$n_{\text{min.}}$	4,5	4,5	5,5	5,5	5,5	5,5	7	7
$s_{\text{ISO/DIN}}$	27	30	34/32	36	41	41	46	50
$w_{\text{max.}}$	15	16	18	19	22	22	24	26
Splint	4x32	4x36	5x36	5x40	5x45	5x50	6,3x50	6,3x56

Maße	M 33	M 36	M 38*	M 39	M 40*	M 42	M 45	M 48
$d_{e \text{ max.}}$	46	50	55	55	55	58	62	65
m	35	38	40	40	48	46	48	50
$n_{\text{min.}}$	7	7	7	7	7	9	9	9
$s_{\text{ISO/DIN}}$	50	55	60	60	60	65	70	75
$w_{\text{max.}}$	26	29	31	31	31	34	36	38
Splint	6,3x56	6,3x63	6,3x70	6,3x71	6,3x70	8x71	8x80	8x80

Maße	M 52	M 56	M 60	M 64	M 68	M 72	M 76	M 80
$d_{e \text{ max.}}$	70	75	80	85	90	95	100	105
m	54	57	63	66	69	73	76	79
$n_{\text{min.}}$	9	9	11	11	11	11	11	11
$s_{\text{ISO/DIN}}$	80	85	90	95	100	105	110	115
$w_{\text{max.}}$	42	45	48	51	54	58	61	64
Splint	8x90	8x100	10x100	10x100	10x112	10x112	10x125	10x140

\* gemäß DIN 935:1963