

F204 F-63/0,03



F204 F-63/0,03 Residual Current Circuit Breaker

General Information

Extended Product Type	F204 F-63/0,03
Product ID	2CSF204325R1630
EAN	8012542993230
Catalog Description	F204 F-63/0,03 Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. Type F offers the same range of protection and functionality as an RCCB Type A APR

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Popular Downloads

Data Sheet, Technical Information	2CSC423012B0201
Instructions and Manuals	Manual sheet inside the box

Dimensions

Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.360 kg

Technical

Standards	IEC/EN 61008 IEC/EN 62423
Operating Characteristic	Instantaneous
Type of Residual Current	F type
Rated Residual Current	30 mA
Rated Current (I_n)	63 A
Number of Poles	4
Position of Neutral Terminals	Right
Power Loss	at Rated Operating Conditions per Pole 4.4 W

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.082 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.403 kg
Package Level 1 EAN	8012542993230

Classifications

Object Classification Code	Q
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

