

SRGC clamping holder, positive, right

For copy, longitudinal face lathing with RC indexable insert

ATORN[®]

Application

For longitudinal turning with RC indexable insert

Version

- Precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



| | |
|---------------------------------------|-------------------|
| Art. no. | 17850 502 |
| ISO name | SRGC R/L 1616 H06 |
| Shaft height | 16 mm |
| Shank width | 16 mm |
| Length | 100 mm |
| Length of head | 13.6 mm |
| Programming size | 20 mm |
| Suitable for indexable inserts | RC.. 0602.. |
| Tool design | Right |

EAN-Code

4050293562996