Service

Rexroth Bosch Group

1/6

RE 25710-D/06.14

Replaces: 05.09

Pressure relief valve, direct operated

Type DBD....SO156

Size 4 Component series 1X Maximum operating pressure 420 bar Maximum flow 20 I/min

Table of contents

Contents
Features
Ordering code
Function, section, symbol
Technical data
Characteristic curves
Unit dimensions
Mounting cavity

Features

Page -	- Screw-in	cartridge
--------	------------	-----------

- It is used in applications with particularly high leak-tightness requirements
- Leakage-proof up to a maximum of 80% of the set opening pressure
- 2 adjustment types, optionally:
- setscrew with internal hexagon
- hand wheel

1

2

2

3

3


4

5

Information on available spare parts: www.boschrexroth.com/spc




Ordering code



Function, section, symbol

The pressure valve type DBD...SO156 is a direct operated pressure relief valve for the installation in block designs. It is used in applications with particularly high leak-tightness requirements for limiting a system pressure. The system pressure can be set via the adjustment type (4).

In the initial position the valve is closed. The pressure in the main port ① acts on the spring plate (5) via the control line (2) and poppet (1). If the pressure in the main port ① exceeds the value set at the compression spring (3), the poppet (1) opens and hydraulic fluid flows into the main port ②.



(1) = Main port 1 (P)
(2) = Main port 2 (T)

Technical data (For applications outside these parameters, please consult us!)


General	al		
Weight kg	approx. 0.05		
Installation position	any		
Ambient temperature range °C	-20 +80		

Hydraulic


Maximum operating pressure	bar	420
Maximum flow	l/min	20
Hydraulic fluid		Mineral oil (HL, HLP) according to DIN 51524; fast biodegradable hydraulic fluids according to VDMA 24568 (see also RE 90221); HETG (rape seed oil); HEPG (polyglycols); HEES (synthetic esters), other hydraulic fluids on request
Hydraulic fluid temperature range	°C	-20 +80
Viscosity range	mm²/s	20 200
Maximum admissible degree of contamination of the hydraulic fluid cleanliness class according to ISO 4406 (c)		Class 20/18/15 1)

¹⁾ The cleanliness classes stated for the components need to be maintained in hydraulic systems. Effective filtration prevents faults and at the same time increases the life cycle of the components.

For the selection of the filters see www.boschrexroth.com/filter



Characteristic curves (measured with HLP46, $\vartheta_{oil} = 40 \pm 5 \text{ °C}$)




The characteristic curves apply to output pressure = 0 in the total flow range!

Definition cracking pressure:

Pressure in bar at $q_{\rm V}$ =0.95 +0.05 l/min


Unit dimensions (dimensions in mm)



- 1.1 Adjustment type "S", internal hexagon SW5
- 1.2 Adjustment type "H", hand wheel
 - 2 Lock nut SW17
 - 3 Hexagon SW17, tightening torque when screwing in $M_{\rm A}$ =23±2 Nm
 - 4 Impressed type designation
- ① = Main port 1 (P)
- ② = Main port 2 (T)
- LS = Location shoulder

Mounting cavity R/DBD . 4K; 2 main ports, thread M14 x 1

(dimensions in mm)



(1) = Main port 1 (P)

(2) = Main port 2 (T), optionally arrange at the circumference
LS = Location shoulder

Tolerance for all angles $\pm 0.5^{\circ}$

¹⁾ Depth for moving parts

²⁾ All seal ring insertion faces are rounded and free of burrs

³⁾ With countersink

4) Visual inspection

Standards:

Workpiece edges	DIN ISO 13715
Form and position tolerance	DIN EN ISO 1101
General tolerance for metal-cutting procedures	DIN ISO 2768-mK
Tolerance	DIN ISO 8015
Surface condition	DIN EN ISO 1302

Notes

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52/18-0 documentation@boschrexroth.de www.boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without consent of Bosch Rexroth AG.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Notes

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52/18-0 documentation@boschrexroth.de www.boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without consent of Bosch Rexroth AG.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

Bosch Rexroth AG Hydraulics Zum Eisengießer 1 97816 Lohr am Main, Germany Phone +49 (0) 93 52/18-0 documentation@boschrexroth.de www.boschrexroth.de © This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without consent of Bosch Rexroth AG.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.