

Workplace mat made of 100% natural rubber

Flat structure, height 19 mm – modular assembly system



Application:

Extremely comfortable anti-fatigue mat for heavy-duty work, with diamond-pattern surface. For use both in large areas and individual workplaces. These 45 x 45 cm modular floor tiles are equipped with a universal double locking system on all four sides, designed to enable an extra-firm, seamless connection for fast installation.

Execution:

- This 19-mm thick mat lifts the employee off the hard floor, while balls underneath the mat allow for flexibility with every movement.
- The diamond-pattern surface provides good grip, and allows easy pivoting and freedom of movement when working on dynamic jobs
- Slip resistance R10 in accordance with DIN 51130
- Free of DOP, DMF, ozone-depleting substances, silicone and heavy metals



Advantage:

- The square mats can be assembled to cover any area
- Can be combined with black or yellow edge strip made of nitrile rubber, 91 cm x 15 cm
- The flexible assembly system means that individual mats can be exchanged or adapted to a different environment
- Insulating mat protects against cold, heat, vibration and noise

Art. no.	50225 261
Brand	NOTRAX
Manufacturer Part Number	570S1818BL
Surface structure	Stud plate / closed
Material	Rubber
Length	450 mm
Width	450 mm
Material thickness	19 mm
Mat design	Individual mat
Resistance against	Acid (limited)
Suitable for wet areas	No
Antistatic	No
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Black
ESD-capable	No
Gross Weight	3.300 kg
Product Group	5AD

EAN

0662641906662