


Inductive sensor

IEBC003BASKG/0,3M/AS

**Product characteristics**

Electrical design		PNP/NPN
Output function		normally open
Sensing range [mm]		3
Housing		threaded type
Dimensions [mm]		M8 x 1 / L = 37

Electrical data

Operating voltage [V]		10...30 DC
Current consumption [mA]		< 10; (only in 3-wire operation)
Protection class		III
Reverse polarity protection		yes

Outputs

Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC [V]		2.8
Minimum load current [mA]		2
Max. leakage current [mA]		0.5; (only in 2-wire operation)
Permanent current rating of switching output DC [mA]		100; (only in 2-wire operation)
Switching frequency DC [Hz]		1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Sensing range [mm]		3
Operating distance [mm]		0...2.4

Inductive sensor

IEBC003BASKG/0,3M/AS

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15

Operating conditions

Ambient temperature	[°C]	0...60
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	3019
	Ta	-25...80 °C
UL approval	Enclosure type	Type 1
	voltage supply	Limited Voltage/Current
	File number UL	E174191

Mechanical data

Weight	[g]	24.6
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: LCP

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Accessories (supplied)	lock nuts: 2
------------------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.3 m, PVC; 3 x 0.14 mm ²

Connector: 1 x M8; Locking: snap-fit



Inductive sensor

IEBC003BASKG/0,3M/AS

