

**Industrial Ethernet
IE-C5DB4RE0280MCSMCS-E**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- Cat. 6 throughout_A with **STEADYTEC**® technology
- pre-assembled cables and cables sold by the metre
- Copper and fibre-optic cables
- in IP20 and IP67
- all relevant industrial connections: RJ45, M12, SC, ...
- comprehensive range of accessories

General ordering data

Type	IE-C5DB4RE0280MCSMCS-E
Order No.	1010850280
Version	System cable, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), Radox GWK S, 28 m
GTIN (EAN)	4050118514568
Qty.	1 pc(s).

Industrial Ethernet IE-C5DB4RE0280MCSMCS-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	28 m	Length (inches)	1.102 inch
Net weight	2,188 g	Insulation cross-section	1.95 mm

Temperatures

Operating temperature, max.	90 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	90 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...90 °C	Storage temperature	-40 °C...90 °C
Installation temperature	-25 °C...90 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Standards

Fire safety for railway vehicles	According to DIN 5510-2 fire safety levels 1,2,3,4, According to BS 6853, According to EN50288-2-2, According to EN 45545, HL1 - HL3	Fire protection in buses	according to ISO 6722-1 5.22 (UN ECE-R 118.01)
Flames propagate vertically on bundled cables	According to BS4066-3, DIN EN 50266-2-5, According to IEC 60332-3-25 D	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2
Corrosiveness of fumes	to IEC 60754-2	Hydrogen halide content	According to EN-50267-2-1, According to IEC 60754-1
Poisonous gases	According to BS 6853 Appendix B	Fluorine content	According to EN 60684-2 Section 45.2
Multi-wire metallic data and control cable	According to EN50288-2-2		

Cable structure

Strands	7	Cross-section	2*2*AWG 22/7 - 2*2*0.36 mm ²
Insulation cross-section	1.95 mm	Shielding	SF/UTP
Material sheath	Radox GWK S	Sheath diameter, min.	6.95 mm
Sheath diameter, max.	7.55 mm	Sheathing colour	black

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
----------	---

Mechanical and material properties of cable

Min. bending radius, repetitive	6 *diameter	Abrasion resistance	very good
Resistance to oils	in accordance with EN 50306-3	Halogen	halogen-free, according to IEC 60754-2
Corrosiveness of fumes	to IEC 60754-2	Impervious to smoke	According to BS 6853 Appendix D, in accordance with EN 50268-2, According to IEC 61034-2

Industrial Ethernet IE-C5DB4RE0280MCSMCS-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

plug

Connector left	M12 D-code – IP 67 straight pin	Connector right	M12 D-code – IP 67 straight pin
----------------	------------------------------------	-----------------	------------------------------------

Classifications

ETIM 6.0	EC002599	UNSPSC	30-21-18-01
eClass 6.2	27-06-91-90	eClass 9.0	27-06-03-08
eClass 9.1	27-06-03-08		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN