

## Electronic manual hanging scales CH

Up to max. 50 kg

**KERN**

### Application:

For rapid checking of weights with high mobility.

### Execution:

- Large LED display
- Display units: kg/lb/N
- Functions: AUTO OFF
- Pull-out tape measure, length 1 m
- Data hold function (weight display can be frozen for 5 s)
- Tara button for zeroing under load

### Delivery:

With battery



|                                    |                  |
|------------------------------------|------------------|
| <b>Art. no.</b>                    | <b>44228 030</b> |
| <b>Brand</b>                       | KERN             |
| <b>Manufacturer Part Number</b>    | CH 50K50         |
| <b>Type description</b>            | CH 50K50         |
| <b>Max. weight measuring range</b> | 50 kg            |
| <b>Digit increment, weight</b>     | 50 g             |
| <b>Height</b>                      | 270 mm           |
| <b>Housing dimensions (LxWxH)</b>  | 30 x 90 x 176 mm |
| <b>Weight</b>                      | 0.25 kg          |
| <b>Gross Weight</b>                | 0.544 kg         |
| <b>Product Group</b>               | 443              |

### EAN

4045761027190