


PIN Assignment



- Electrical Test:
- 100%Test(Open ,short ,miss wire)
 - Contact Resistance: 2 ohm(max).
 - Insulation Resistance: DC 300V/10ms, 10M ohm(MIN)

NO	DESCRIPTION	Q'TY	UNIT	APPD BY	DATE	REV.
6	A6-0000015 HDMI AM transparent dust cover	1	pcs			
5	A2-R028789 HDMI AM Black insulation Nickel plated iron shell PIN G/F	1	pcs			
4	A5-R047011 Transparent PE	10	g			
3	A5-R047001 45P Black PVC RoHS	25	g			
2	A2-R028742 DVI(24+1)F Black insulation Nickel plated iron shell PIN 3u Before the riveting hexagonal nickel plated nut	1	pcs			
1	A4-R002264 UL20276 (30AWG*1P+EAM)*4C+30AWG*1P+30AWG*3C+AEB(50%AL) OD:5.5MM BLACK PVC MARK: DVI CABLE	0.2	m			
					2019.04.09	1/1

TOLERANCE		INCHES		M/M	
.X	.015	.30			
.XX	.010	.10			
.XXX	.005	.05			
DRAWN BY		CUSTOMER :		CPC	
CHECK BY		CUSTOMER P/N :		CS32852	
APPD BY		SCALE	NONE		REV.
		UNIT	MM		A1
		DATE	2019.04.09		1/1

TITLE: HDMI M TO DVI(24+1)F CABLE