

## Agile fork lift truck with electric travel drive

### Application:

Use as a standard fork lift truck, allowing loads of up to 1.2 tons to be moved.

### Execution:

- Fast and efficient motorised drive wheels with low noise and easy maintenance
- 2 drive wheels for maximum stability, better traction and a longer service life
- Can be switched between electric and manual operation
- 3 hours of continuous use (with an average load of 600 kg at maximum speed)
- Maximum speed of 5.3 km/h
- Quick loading within 2 hours possible
- Display with LED indicator

### Advantage:

- Reduced effort and improved health and safety conditions
- Low purchasing costs, low maintenance costs, high productivity
- Electric brake for use on slopes
- Low tare weight: just 88 kg



<b>Art. no.</b>	<b>50262 200</b>
<b>Brand</b>	PRAMAC LIFTER
<b>Fork roller diameter</b>	82 mm
<b>Manufacturer Part Number</b>	EJ741000T00
<b>Turning radius</b>	1382 mm
<b>Load-carrying capacity</b>	1200 kg
<b>Length</b>	1600 mm
<b>Fork length</b>	1150 mm
<b>Fork arm width</b>	150 mm
<b>Fork, external distance</b>	525 mm
<b>Material of fork castor</b>	Rubber
<b>Castor-wheel diameter</b>	200 mm
<b>Material of steering wheels</b>	Polyurethane
<b>Travel drive</b>	Electric
<b>Speed at nominal load</b>	4.2 km/h
<b>Speed without load</b>	5.3 km/h
<b>Rechargeable battery/battery capacity</b>	10.4 Ah
<b>Battery voltage</b>	36 V
<b>Drive motor capacity</b>	0.25 kW
<b>Max. surmountable tilt with load</b>	5 %
<b>Max. surmountable tilt without load</b>	15 %
<b>Min./max. tiller height in driving position</b>	710-1185 mm
<b>Operation</b>	Concomitant
<b>Model</b>	Agile S2-S4
<b>Weight</b>	88 kg
<b>Gross Weight</b>	88.000 kg
<b>Product Group</b>	559

### EAN

8018539083984