

BSE 14-3 100 calender set

1400 W, 230 V

FLEX

Application:

For optimal processing of various materials when satin-finishing, texturing, polishing, brushing, smoothing, removing rust, deburring steel and stainless steel surfaces

Execution:

- Microprocessor electronics: Speed pre-selection, constant speed maintenance using a tachometric generator, soft start-up, restart inhibitor after power failure, overload protection and temperature monitoring
- A unique tool attachment with quick-action coupling for tool-free changing of the system's attachments for burnishing and tube belt sanding
- Tool-free grinding tool replacement via patented quick-change system
- Adjustable protective cover: for striking tools up to dia. 125 mm
- spindle lock

Advantage:

- The grinding attachment for burnishing can be adjusted variably, allowing work to be carried out close to edges; also suitable for narrow rollers

Delivery:

Grinding attachment satin-finishing BS 00, rubber air roller, air pump, abrasive fleece A 280/fine, Superfinishing sleeves S 600 and S 500, MESHFLEX A 400 sanding sleeve, 3 each of sanding sleeves: ZIRCOFLEX P 80, ZIRCOFLEX P 20, CERAFLEX K 20, CORUFLEX P 80, transport case L-BOXX® 238.



Art. no.	70563 011
Brand	FLEX
Manufacturer Part Number	433438
Manufacturer Article Number	433438
Power input	1400 W
Power output	880 W
Min./max. idle speed	3500-1000 rpm
Max. diameter of roll	125
Max. tool width	125 mm
Tool holding device	Inner diameter 19 mm
Weight	2.9 kg
Gross Weight	8.165 kg
Product Group	707

EAN

4030293187184