

## Miniature cutting insert, type AW HW56 15

for chamfering and profile turning

**ATORN**<sup>®</sup>



### Application

For chamfering and profile turning in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.

### Version

- solid carbide cutting insert, 45° chamfer angle with inner cooling

### Advantage

- very hard cemented carbide type ensures low wear
- user-friendly chamfering and profile turning and precise chamfers with excellent finish quality
- extremely sharp cutting edges ensure cutting with process reliability

<b>Art. no.</b>	<b>17128 160</b>
<b>Shaft diameter</b>	6 mm
<b>ISO name</b>	AW
<b>Length</b>	51 mm
<b>Clearance length</b>	15 mm
<b>Radius</b>	0.2 mm
<b>Chamfer angle</b>	45 Degree
<b>Bevel angle</b>	45 Degree
<b>Programming size</b>	2.3 mm
<b>Min. bore diameter</b>	1 mm
<b>Holder size</b>	6
<b>Machining direction</b>	Right
<b>Carbide type</b>	HW56 15
<b>Material to be processed</b>	Stainless steel, Non-ferrous metal

### EAN-Code

4050293377095