

## Forklift truck with quick lift function

Model GS EVO



### Application:

For lifting and carrying loads on pallets or in standardised containers

### Execution:

- For intensive use
- Compact design
- Chrome-plated piston rod and oil seal: Prevents rust formation and oil leaks during use
- Adjustable lowering speed: The lowering speed can be controlled proportionately to the lever position on the drawbar. Perfect for fragile and sensitive loads such as crystal, glass and ceramic
- Retracting and extending rollers: Facilitate entry into closed pallets
- 3D superior ergonomic control: Thanks to the two large grip side areas that ensure a perfect position, this version enables the user to enjoy an even better operating position with less force required compared to conventional handles
- With quick-lift function: For fast lifting of your loads. Only 3 pumping strokes are needed and the pallet is free from the ground. Hydraulic changeover point: 120 kg.
- Simple installation



<b>Art. no.</b>	<b>50262 309</b>
<b>Brand</b>	PRAMAC LIFTER
<b>Fork roller diameter</b>	82 mm
<b>Manufacturer Part Number</b>	TMB41AVY100
<b>Turning radius</b>	1367 mm
<b>Material</b>	Steel
<b>Load-carrying capacity</b>	2500 kg
<b>Fork length</b>	1150 mm
<b>Fork arm width</b>	150 mm
<b>Fork, external distance</b>	525 mm
<b>Min. lift height</b>	85 mm
<b>Lift height</b>	200 mm
<b>Fork castor design</b>	Tandem
<b>Castor-wheel diameter</b>	200 mm
<b>Material of steering wheels</b>	Polyurethane
<b>Steering wheel design</b>	With nylon inner core
<b>With quick-lift function</b>	Yes
<b>With weighing system</b>	No
<b>Colour</b>	Green Pantone 382
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	63.000 kg
<b>Product Group</b>	559

### EAN

5056528162534