Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's address: Schiefer Lighting, Potterbakkerstraat 35, 4871EP Etten-Leur, NL

Model identifier: 644578300


Type	of light	source:
------	----------	---------

Lighting technology used:	HL	Non-directional or directional:	NDLS	
Light source cap-type	GY6.35			
(or other electric interface)				
Mains or non-mains:	MLS	Connected light source (CLS):	No	
Colour-tuneable light source:	No	Envelope:	-	
High luminance light source:	No			
Anti-glare shield:	No	Dimmable:	Yes	
Product parameters				

Product parameters						
Parameter		Value	Parameter	Value		
General product parameters:						
Energy consur mode (kWh/10 up to the neare	00 h), rounded	75	Energy efficiency class	G		
dicating if it refe a sphere (360º)	s flux (фuse), ineers to the flux in, in a wide cone arrow cone (90º)	1 050 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000		
On-mode pow pressed in W	ver (P _{on}), ex-	75,0	Standby power (P _{sb}), expressed in W and rounded to the sec- ond decimal	0,00		
Networked standby power (P _{net}) for CLS, expressed in W and rounded to the second decimal		-	Colour rendering in- dex, rounded to the nearest integer, or the range of CRI-val- ues that can be set	100		
Outer dimen-	Height	58	Spectral power dis-	See image		
sions without	Width	14	tribution in the	in last page		
separate con- trol gear, light- ing control	Depth	14	range 250 nm to 800 nm, at full-load			

parts and non- lighting con- trol parts, if any (millime- tre)			
Claim of equivalent power ^(a)	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,456 0,410

(a)'-': not applicable; (b)'-': not applicable;



Spectral Distribution