Shock-Safe Fuseholder, 5 x 20 mm, Slotted Cap, vertical, IP 40 / IP 54





Variant 1: Standard

Variant 2: Sealed for potting

250 VAC · 2 W / 6.3 A (VDE) · 250 VAC/VDC · 12 A (UL/CSA)

See below:

Approvals and Compliances

Description

- Vertical style
- IP 40 oder IP 54 from frontside

pdf datasheet, html-datasheet, General Product Information, Packaging details, Distributor-Stock-Check, Detailed request for product, Microsite

| hnical | |
|--------|--|
| | |

| recrimical Data | | | |
|------------------------------|--|--|--|
| Shock-Safe Category | PC2 | | |
| Fuse-Link | 5 x 20 mm | | |
| Mounting | PCB | | |
| Terminal | Solder THT | | |
| Rated Voltage | 250 VAC (VDE), 250 VAC/VDC (UL/CSA) | | |
| Rated current | 6.3 A (VDE), 12 A (UL/CSA) | | |
| Rated Power Acceptance IEC | 2W / 6.3A @ Ta 23°C | | |
| | Admissible power acceptance at higher ambient temperature see derating cur- | | |
| | ves | | |
| Degree of Protection | IP 40 / IP 54 | | |
| Protection Class | Suitable for appliances with protection class I acc. to IEC 61140 | | |
| Admissible Ambient Air Temp. | -40 °C to 85 °C | | |
| Climatic Category | 40/085/21 acc. to IEC 60068-1 | | |
| Material: Socket | Thermoplastic, black, UL 94V-0 | | |
| Material: Cap | Thermoplastic, black, UL 94V-0 | | |
| Material: Terminals | Tin-Plated Copper Alloy | | |
| Unit Weight | 5.03 g | | |
| Storage Conditions | 0°C to 60°C, max. 70% r.h. | | |
| Product Marking | I , Type, Rated Voltage, Rated current, Power Rating, Certification marks | | |
| | | | |

| Soldering Methods | Wave Soldering Profile |
|------------------------------|--|
| Solderability | 245°C / 3 sec acc. to IEC 60068-2-20, Test Ta, method 1 |
| Resistance to Soldering Heat | 260 °C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 1 |
| Contact Resistance | ≤ 10 mΩ at 20 mV acc. to IEC 60127-6 |
| Dielectric Strength | > 3kV between life parts (50 Hz: 1 min) |
| Impulse Withstand Voltage | > 4 kV between life parts |
| Insulation Resistance | ≥ 10 MΩ between life parts (500 VDC: 1 min) |
| Overvoltage Category | III acc. to IEC 60664-1 |
| Pollution Degree | 3 acc. to IEC 60664-1 |
| Resistance to Vibration | acc. to IEC 60068-2-6, test Fc |

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: FAF

| Approval Logo | Certificates | Certification Body | Description |
|-----------------|---------------|--------------------|-------------------------|
| VDE | VDE Approvals | VDE | VDE Certificate Number: |
| c FU °us | UL Approvals | UL | UL File Number: E39328 |

Product standards

Product standards that are referenced

| Organization | Design | Standard | Description |
|--------------|-----------------------|----------------------|--|
| <u>IEC</u> | Designed according to | IEC 60127-6 | Miniature fuses. Part 6. Fuse-holders for miniature fuse-links |
| (UL) | Designed according to | UL 4248-1 | Fuseholder general requirements |
| GF Group | Designed according to | CSA C22.2 no. 4248.1 | Fuseholder general requirements |

Application standards


Application standards where the product can be used

| Organization | Design | Standard | Description |
|--------------|--------------------------------|--------------|---|
| <u>IEC</u> | Designed for applications acc. | IEC/UL 60950 | IEC 60950-1 includes the basic requirements for the safety of information technology equipment. |
| <u>IEC</u> | Designed for applications acc. | IEC 60335-1 | Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-12 and -13. |

Compliances

The product complies with following Guide Lines

| Identification | Details | Initiator | Description |
|----------------|------------------------------|-------------|---|
| C€ | CE declaration of conformity | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
| RoHS | RoHS | SCHURTER AG | EU Directive RoHS 2011/65/EU |
| © | China RoHS | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS. |
| REACH | REACH | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force. |
| 00 | White paper Glow wire test | SCHURTER AG | Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-12 and -13. |




Variant 1: 0031.3701 and 0031.3703



Drilling diagram

Derating Curves



All Variants

| Holder | Сар | Terminal | Tightness | Degree of Protection | Order Number | _ |
|--------|---------|----------|-----------|----------------------|--------------|---|
| • | slotted | straight | - | IP 40 | 0031.3701 | |
| • | slotted | kinked | - | IP 40 | 0031.3703 | |
| • | slotted | straight | sealed | IP 40 | 0031.3751 | |
| • | slotted | straight | sealed | IP 54 | 0031.3753 | |

Most Popular.

 $\label{thm:com/enso} A \textit{vailability for all products can be searched real-time:} https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER$

Packaging Unit Bulk (100 pcs.)