

Model Number


V1-W-5M-PUR-ABG-V1-W


Connecting cable, M12 to M12, PUR cable 4-pin, shielded

Features

- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- · Shield attached to coupling nut
- · Gold-plated and machined contacts
- Degree of protection IP67 / IP68 / IP69K
- Halogen-free

Dimensions







Technical data

General specifications

Number of pins	4 + Shleid
Connection 1	socket
Construction type 1	right angle
Threading 1	M12
Connection 2	Male connector
Construction type 2	right angle
Threading 2	M12

Electrical specifications

Operating voltage	U_B	max. 250 V AC/D0
Operating current		max. 4 A
Contact resistance		< 10 mΩ

Ambient conditions

Ambient temperature	-25 100 °C (-13 212 °F)
	for temperatures over 80 °C (176 °F) reduced elongation at tear

4 chield

Pollution Degree 3

wechanical specifications	
Contact elements	spring-loaded contact socket
Pin diameter	1 mm

Degree of protection IP67 / IP68 / IP69k

Material

Contacts	CuSn / Au
Contact surface	Au
Body	TPU, green
Cable	PUR
Slotted nut	Diecast zinc
Sleeve connector	Diecast zinc
Core insolation	PP
Cable	fine-strand, flexible
Sheath diameter	Ø4.8 mm
Rending radius	> 10 x cable diamet

Bending radius > 10 x cable diameter, moving

Shield grid
Length L 5 m
Flammability

Contact material 94 HB
Housing 94 V-2


Compliance with standards and direc-

tives
Standard conformity

Degree of protection EN 60529:2000

Electrical connection







Standards IEC 61076-2-101:2008