



Figure similar

SIRIUS POSITION SWITCH METAL ENCLOSURE  
40MM ACC. TO EN50041 DEVICE CONNECTION 1X  
(M20X1.5) 1NO/1NC SNAP-ACTION CONTACTS  
ANGULAR METAL ROLLER LEVER AND PLASTIC  
ROLLER 22MM

|   |  |  |
|---|--|--|
| Product designation   |  | standard position switch   |
| <b>Manufacturer article number</b>  |  |  |
| <ul style="list-style-type: none"> <li>• of the supplied basic switch</li> <li>• of the supplied actuator head for position switches</li> <li>• of the supplied switching contacts</li> <li>• of the supplied empty enclosure with cover</li> </ul> |  | <a href="#">3SE5112-0CA00</a><br><a href="#">3SE5000-0AF01</a><br><br><a href="#">3SE5000-0CA00</a><br><a href="#">3SE5112-0AA00</a> |

General technical data:

|  |    |              |
|--|----|--------------|
| <b>Product function</b>  |    |              |
| <ul style="list-style-type: none"> <li>• positive opening</li> </ul>   |    | Yes          |
| <b>Insulation voltage</b>  |    |              |
| <ul style="list-style-type: none"> <li>• Rated value</li> </ul>  | V  | 400          |
| <b>Degree of pollution</b>   |    | class 3      |
| <b>Shock resistance</b>  |    | 30g / 11 ms  |
| <b>Vibration resistance</b>  |    | 0.35 mm / 5g |
| <b>Surge voltage resistance Rated value</b>  | kV | 6            |
| <b>Mechanical service life (switching cycles)</b>  |    |              |
| <ul style="list-style-type: none"> <li>• typical</li> </ul>  |    | 15 000 000   |
| <b>Electrical endurance (switching cycles)</b>   |    |              |
| <ul style="list-style-type: none"> <li>• at AC-15 at 230 V typical</li> </ul>  |    | 100 000      |
| <b>Electrical endurance (switching cycles) with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026 typical</b> |    | 10 000 000   |
| <b>Electrical operating cycles in one hour with contactor 3RH11, 3RT1016, 3RT1017, 3RT1024, 3RT1025, 3RT1026</b>         |    | 6 000        |

|  |    |            |
|--|----|------------|
| <b>Thermal current</b>   | A  | 6          |
| <b>Material of the enclosure of the switch head</b>  |    | metal      |
| <b>Protection class IP</b>   |    | IP66/IP67  |
| <b>Equipment marking</b>   |    | B          |
| <ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>               |    | B          |
| <b>Active principle</b>  |    | mechanical |
| <b>Repeat accuracy</b>   | mm | 0.05       |
| Explosion protection category for dust   |    | none       |
| Explosion protection category for gas  |    | none       |
| Minimum actuating force in activation direction  | N  | 10         |
| <b>Operating current at AC-15</b>  |    |            |
| <ul style="list-style-type: none"> <li>• at 230 V Rated value</li> <li>• at 400 V Rated value</li> </ul>                   | A  | 6          |
|  | A  | 4          |
| <b>Operating current</b>   |    |            |
| <ul style="list-style-type: none"> <li>• at DC-13 at 125 V Rated value</li> <li>• at DC-13 at 400 V Rated value</li> </ul> | A  | 0.55       |
|  | A  | 0.1        |
| <b>Operating current</b>   |    |            |
| <ul style="list-style-type: none"> <li>• at DC-13</li> <li>— at 24 V Rated value</li> </ul>                                | A  | 3          |

#### Enclosure:

|   |  |                            |
|---|--|----------------------------|
| <b>Design of the housing</b>                  |  | block, narrow              |
| <b>Material of the enclosure</b>              |  | metal                      |
| <b>Coating of the enclosure</b>               |  | cathodic immersion coating |
| <b>Design of the housing acc. to standard</b> |  | Yes                        |

#### Drive Head:

|  |  |                             |
|--|--|-----------------------------|
| <b>Design of the operating mechanism</b> |  | metal lever, plastic roller |
| <b>Standard-compliant actuator head</b>  |  | EN 50041                    |
| <b>Shape of the switch head</b>          |  | roller                      |
| <b>Design of the switching function</b>  |  | positive opening            |

#### Connections/ Terminals:

|   |  |   |
|---|--|---|
| <b>Type of electrical connection</b>  |  | screw-type terminals  |
| <b>Type of connectable conductor cross-section</b>  |  |   |
| <ul style="list-style-type: none"> <li>• solid</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> <li>• for AWG conductors</li> <li>— solid</li> <li>— stranded</li> </ul> |  | 1x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.5 ... 0.75 mm <sup>2</sup> ) |
|   |  | 1x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.5 ... 0.75 mm <sup>2</sup> ) |
|   |  | 1x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.5 ... 0.75 mm <sup>2</sup> ) |
|   |  | 1x (20 ... 16), 2x (20 ... 18)  |
|   |  | 1x (20 ... 16), 2x (20 ... 18)  |

#### Mechanical data:

|                         |  |                |
|-------------------------|--|----------------|
| <b>Cable entry type</b> |  | 1x (M20 x 1.5) |
|-------------------------|--|----------------|

### Communication/ Protocol:

**Design of the interface** without

### Ambient conditions:

**Ambient temperature**

- during operation °C -25 ... +85
- during storage °C -40 ... +90

### Installation/ mounting/ dimensions:

**mounting position** any

**Mounting type** screw fixing

### Certificates/ approvals:

**General Product Approval**

**Declaration of  
Conformity**

**Test  
Certificates**

**other**



[Special Test  
Certificate](#)

[Confirmation](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE51120CF01>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3SE51120CF01/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SE51120CF01&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE51120CF01&lang=en)



last modified:

09.03.2015