

PRODUCT-DETAILS

EXLT0530

LFH FLEXIBLE CONDUIT 25MM 30M BLK



General Information

Extended Product Type	EXLT0530
Product ID	7TCA297120R0139
EAN	5011949001244
Catalog Description	LFH FLEXIBLE CONDUIT 25MM 30M BLK
Long Description	Liquid Tight Metallic Conduit, Low Fire Hazard, Conduit Size 25mm, Minimum Bore 21mm, Reel Length 30 Meters, Galvanised Steel Core with LFH Coating, Black

Ordering

EAN	5011949001244
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	34.93 lb 15.841 kg
--------------------	-----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in

	25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Connection for Conduit Systems when Low Fire Hazard is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	21 mm
Material	Galvanized Steel Core with Low Fire Hazard Coating
Nominal Size	25 mm
Number of Batteries	0
Product Name	flexible metal conduit
Product Type	Liquid Tight Metallic Conduit
Special Functions	Limited Fire Hazard, Zero Halogen (BS6425 Pt1)
Standards	LUL compliant (E1042A6)
UPC	786210287645

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLT0530
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLT0530

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

