

Transverse drive shell end mill arbor DIN 6357 (face mill arbor)

With enlarged collar diameter DIN 69893-1

ATORN[®]

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Internal coolant supply
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- max. concentricity < 0.005 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- With Balluff chip hole

Delivery

includes key blocks and cutter retaining screw



Art. No.	23162 135
Tool holding device	HSK 63
Form	A
Mandrel diameter	27 mm
Tap length	21 mm
Projecting length	130 mm
Outer diameter	58 mm
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293711691