

## Rough grinding disc for aluminium/non-ferrous metals

Type RS24

# RHODIUS


### Application:

For deburring, chamfering and pre/post-machining of welding seams.

### Execution:

- Special filler materials to prevent clogging of the disc
- High cutting performance
- Minimal heat generation

<b>Art. no.</b>	<b>76102 103</b>
<b>Brand</b>	RHODIUS
<b>Manufacturer Part Number</b>	200357
<b>Removal performance (points system)</b>	●●●●
<b>Service life (points system)</b>	●●●●
<b>Washer diameter</b>	125 mm
<b>Washer thickness</b>	7 mm
<b>Bore diameter</b>	22.23 mm
<b>Max. rotation speed</b>	12250 rpm
<b>Design</b>	Medium hard
<b>Form</b>	Cranked
<b>Free from iron and sulphur</b>	No
<b>Number of pieces per packet</b>	25
<b>Gross Weight</b>	0.210 kg
<b>Product Group</b>	6BB



### EAN

4011890001967