PRODUCT DATASHEET CP17415_YASMEEN-70-W-C

YASMEEN-70-W-C

~36° wide beam. Assembly with holder C compatible with LEDiL HEKLA. Black version.

SPECIFICATION:



MATERIALS:


Component	Type	Material	Colour	Finish
YASMEEN-70-W	Single lens	PMMA	clear	
YASMEEN-70-HLD-C	Holder C	PC	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP17415_YASMEEN-70-W-C	Single lens	105	105	15	10.0
» Box size: 476 x 273 x 305 mm					




PRODUCT DATASHEET CP17415_YASMEEN-70-W-C




See also our general installation guide: www.ledil.com/installation_guide














LED Vesta DTW 9mm (4W/6W/12W)


FWHM / FWTM 37.0° / 53.0°
Efficiency 86 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
Bender Wirth: 652b Hekla



CITIZEN


LED CLL02x/CLU02x (LES10)

FWHM / FWTM 36.0° / 52.0°
Efficiency 84 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
F17435_HEKLA-G2-C



CITIZEN

LED CLL03x/CLU03x
FWHM / FWTM 33.0° / 54.5°
Efficiency 84 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




CREE - LED


F17438_HEKLA-G2-I

LED CMA1516
FWHM / FWTM 36.0° / 52.0°
Efficiency 84 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17436_HEKLA-G2-D








6/13








PHILIPS

LED Fortimo SLM L09 CoB

FWHM / FWTM 36.0° / 52.0°
Efficiency 84 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour. White

Light colour White Required components: F17437_HEKLA-G2-H




SAMSUNG

LED LC016D / LC019D / LC026D / LC033D

FWHM / FWTM 33.0° / 55.0°
Efficiency 83 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

equired components: F17438_HEKLA-G2-I



SAMSUNG

 LED
 LC030C/040C G2


 FWHM / FWTM
 34.0° / 53.0°

 Efficiency
 84 %

 Peak intensity
 2.4 cd/lm

 LEDs/each optic
 1

Light colour White Required components: F17438_HEKLA-G2-I




SEOUL SEMICONDUCTOR


LED MJT COB LES 14.5

FWHM / FWTM 33.0° / 55.0°
Efficiency 83 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17438_HEKLA-G2-I









OPTICAL RESULTS (SIMULATED):



LED V6 HD Gen 7

FWHM / FWTM 38.0° / 52.0°


Efficiency 87 %

Peak intensity 2.3 cd/lm

LEDs/each optic 1
Light colour White

Required components:

F15255_HEKLA-SOCKET-C



CITIZEN

LED CLU712/713


FWHM / FWTM 38.0° / 54.0°

Efficiency 85 %
Peak intensity 2.3 cd/lm

LEDs/each optic 1

Light colour White

Required components: F17438_HEKLA-G2-I



CREE + LED

LED CHA0304

FWHM / FWTM 40.0° / 52.0°

Efficiency 86 %


Peak intensity 2.2 cd/lm

LEDs/each optic 1

Light colour White

F17435_HEKLA-G2-C

Required components:



CREE & LED

LED CHA0410

FWHM / FWTM 38.0° / 52.0°


Efficiency 86 %
Peak intensity 2.3 cd/lm

LEDs/each optic 1

Light colour White

Required components:

F17435_HEKLA-G2-C





OPTICAL RESULTS (SIMULATED):



LED CHA0612


FWHM / FWTM 38.0° / 52.0° Efficiency 86 %

Efficiency 86 %
Peak intensity 2.3 cd/lm

z.5 cd/iii

LEDs/each optic 1
Light colour White

Required components: F17435_HEKLA-G2-C



CREE + LED

LED CMU10xx

FWHM / FWTM 36.0° / 54.0°


Efficiency 86 %

Peak intensity 2.4 cd/lm

LEDs/each optic 1

Light colour White

Required components: F17435_HEKLA-G2-C



CREE = LED

LED CXA/B 13xx

FWHM / FWTM 40.0° / 54.0°


Efficiency 86 %

Peak intensity 2.1 cd/lm

LEDs/each optic 1
Light colour White

Required components:

F17439_HEKLA-G2-J



CREE & LED

LED CXA/B 15xx


FWHM / FWTM 38.0° / 54.0°

Efficiency 85 %
Peak intensity 2.4 cd/lm

LEDs/each optic 1

Light colour White

Required components: F17436_HEKLA-G2-D






OPTICAL RESULTS (SIMULATED):



LED CXA/B 1830
FWHM / FWTM 36.0° / 56.0°
Efficiency 85 %
Peak intensity 2.3 cd/lm
LEDs/each optic 1
Light colour White

Required components: Bender Wirth: 637b Hekla



WNICHIA

LED NVCWJ024Z-V1MT: COB J-Type Tunable White

FWHM / FWTM 41.0° / 58.0°

Efficiency 86 %


Peak intensity 2 cd/lm

LEDs/each optic 1

Light colour White

Required components:

C16142_HEKLA-SOCKET-K Bender Wirth: 498 Typ L8 HV




SAMSUNG

LED LC003D / LC006D / LC009D / LC013D

FWHM / FWTM 36.0° / 54.0°
Efficiency 85 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White

Required components: F17435_HEKLA-G2-C



TRIDONIC

 LED
 SLE G7 LES13


 FWHM / FWTM
 35.0° / 56.0°

 Efficiency
 85 %

 Peak intensity
 2.4 cd/lm

LEDs/each optic 1
Light colour White
Required components:

F17438_HEKLA-G2-I





PRODUCT DATASHEET CP17415_YASMEEN-70-W-C

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

13/13

www.ledil.com/ where_to_buy