

Safety Data Sheet

According to Annex II to REACH - Regulation 2020/878 and to Annex II to UK REACH

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name **CA28**

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Curing Agent.**

1.3. Details of the supplier of the safety data sheet

Name **CHT UK BRIDGWATER LTD**
Full address **Amber House Showground Road**
District and Country **TA6 6AJ Bridgwater (Somerset)**
England
Tel. **+44(0)1278411400**
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **info.uk@cht.com**Supplier: **CHT Germany GmbH**
Bismarckstraße 102
72072 Tübingen
Germany

1.4. Emergency telephone number

For urgent inquiries refer to **Australia: 0418529118**
All other enquiries +44(0)1278 411400

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is classified as hazardous pursuant to the provisions set forth in (EC) Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of (EU) Regulation 2020/878.

Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

Hazard classification and indication:

Acute toxicity, category 4	H302	Harmful if swallowed.
Skin irritation, category 2	H315	Causes skin irritation.
Skin sensitization, category 1	H317	May cause an allergic skin reaction.
Hazardous to the aquatic environment, chronic toxicity, category 3	H412	Harmful to aquatic life with long lasting effects.

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms:

Signal words: **Warning**Hazard statements:
H302 Harmful if swallowed.

SECTION 2. Hazards identification ... / >>

H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H412 Harmful to aquatic life with long lasting effects.

Precautionary statements:

P280 Wear protective gloves.
P261 Avoid breathing dust / fume / gas / mist / vapours / spray.
P333+P313 If skin irritation or rash occurs: Get medical advice / attention.
P264 Wash . . . thoroughly after handling.

Contains: DIMETHYLTIN NEODECANOATE

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage \geq than 0,1%.

The product does not contain substances with endocrine disrupting properties in concentration \geq 0.1%.

SECTION 3. Composition/information on ingredients**3.1. Substances**

Information not relevant

3.2. Mixtures

Contains:

Identification	x = Conc. %	Classification (EC) 1272/2008 (CLP)
DIMETHYLTIN NEODECANOATE		
CAS	68928-76-7 $95 \leq x < 99$	Acute Tox. 4 H302, Skin Irrit. 2 H315, Skin Sens. 1 H317, Aquatic Chronic 3 H412
EC	273-028-6	LD50 Oral: 890 mg/kg
INDEX		
REACH Reg.	01-2120770324-57	

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures**4.1. Description of first aid measures**

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures**5.1. Extinguishing media**

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

SECTION 5. Firefighting measures ... / >>**UNSUITABLE EXTINGUISHING EQUIPMENT**

None in particular.

5.2. Special hazards arising from the substance or mixture**HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE**

Do not breathe combustion products.

5.3. Advice for firefighters**GENERAL INFORMATION**

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage**7.1. Precautions for safe handling**

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

Regulatory References:

DEU	Deutschland	Technischen Regeln für Gefahrstoffe (TRGS 900) - Liste der Arbeitsplatzgrenzwerte und Kurzzeitwerte. MAK- und BAT-Werte-Liste 2020, Ständige Senatskommission zur Prüfung gesundheitsschädlicher Arbeitsstoffe, Mitteilung 56
DNK	Danmark	Bekendtgørelse om grænseværdier for stoffer og materialer - BEK nr 1458 af 13/12/2019
ESP	España	Límites de exposición profesional para agentes químicos en España 2021
FRA	France	Valeurs limites d'exposition professionnelle aux agents chimiques en France. ED 984 - INRS
FIN	Suomi	HTP-VÄRDEN 2020. Koncentrationer som befunnits skadliga. SOCIAL - OCH HÄLSOVÄRDSMINISTERIETS PUBLIKATIONER 2020:25
NOR	Norge	Forskrift om endring i forskrift om tiltaksverdier og grenseverdier for fysiske og kjemiske faktorer i arbeidsmiljøet samt smitterisikogrupper for biologiske faktorer (forskrift om tiltaks- og grenseverdier), 21. august 2018 nr. 1255
PRT	Portugal	Decreto-Lei n.º 1/2021 de 6 de janeiro, valores-limite de exposição profissional indicativos para os agentes químicos. Decreto-Lei n.º 35/2020 de 13 de julho, proteção dos trabalhadores contra os riscos ligados à exposição durante o trabalho a agentes cancerígenos ou mutagénicos
GBR	United Kingdom	EH40/2005 Workplace exposure limits (Fourth Edition 2020)

DIMETHYL TIN NEODECANOATE

Threshold Limit Value

Type	Country	TWA/8h		STEL/15min		Remarks / Observations
		mg/m3	ppm	mg/m3	ppm	
AGW	DEU	0.004	0.02			
TLV	DNK	0.1				SKIN
VLA	ESP	0.1		0.2		
VLEP	FRA	0.1		0.2		
HTP	FIN	0.1		0.3		SKIN
TLV	NOR	0.1		0.3		SKIN
VLE	PRT	0.1		0.2		
WEL	GBR	0.1				SKIN

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Provide an emergency shower with face and eye wash station.

HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Regulation 2016/425 and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

In the presence of risks of exposure to splashes or squirts during work, adequate mouth, nose and eye protection should be used to prevent accidental absorption.

RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type A filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

ENVIRONMENTAL EXPOSURE CONTROLS

SECTION 8. Exposure controls/personal protection ... / >>

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.
Product residues must not be indiscriminately disposed of with waste water or by dumping in waterways.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Properties	Value	Information
Appearance	liquid	
Colour	straw-coloured	
Odour	characteristic	
Odour threshold	not determined	
Melting point / freezing point	-6 °C	
Initial boiling point	250 °C	
Flammability	not flammable	
Lower explosive limit	Not available	
Upper explosive limit	Not available	
Flash point	153 °C	
Auto-ignition temperature	479 °C	
Decomposition temperature	not determined	
pH	Not available	
Kinematic viscosity	Not available	
Dynamic viscosity	liquid	
Solubility	immiscible with water	
Partition coefficient: n-octanol/water	5.5026	
Vapour pressure	Not available	
Density and/or relative density	1.13	
Relative vapour density	not determined	
Particle characteristics	Not applicable	

9.2. Other information

9.2.1. Information with regard to physical hazard classes

Information not available

9.2.2. Other safety characteristics

Evaporation rate	not determined	
Molecular weight g/mol	491.3	
VOC (volatile carbon)	54.46 % - 613.87	g/litre
Explosive properties	not applicable	
Oxidising properties	not applicable	
VOC content	0 %	

SECTION 10. Stability and reactivity

10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials

Information not available

SECTION 10. Stability and reactivity ... / >>**10.6. Hazardous decomposition products**

Information not available

SECTION 11. Toxicological information

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

ATE (Inhalation) of the mixture:	Not classified (no significant component)
ATE (Oral) of the mixture:	898.99 mg/kg
ATE (Dermal) of the mixture:	Not classified (no significant component)

DIMETHYLTIN NEODECANOATE	
LD50 (Dermal):	> 2000 mg/kg (Rabbit)
LD50 (Oral):	890 mg/kg (Rat)

SKIN CORROSION / IRRITATION

Causes skin irritation

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Sensitising for the skin

Respiratory sensitization

Information not available

Skin sensitization

Information not available

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

SECTION 11. Toxicological information ... / >>

Does not meet the classification criteria for this hazard class

Adverse effects on sexual function and fertility

Information not available

Adverse effects on development of the offspring

Information not available

Effects on or via lactation

Information not available

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

Target organs

Information not available

Route of exposure

Information not available

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

Target organs

Information not available

Route of exposure

Information not available

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

11.2. Information on other hazards

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with human health effects under evaluation.

SECTION 12. Ecological information

This product is dangerous for the environment and the aquatic organisms. In the long term, it have negative effects on aquatic environment.

12.1. Toxicity

DIMETHYLTIN NEODECANOATE

EC50 - for Crustacea

39 mg/l/48h Daphnia

EC50 - for Algae / Aquatic Plants

7.6 mg/l/72h Algae

12.2. Persistence and degradability

Information not available

12.3. Bioaccumulative potential

Information not available

12.4. Mobility in soil

SECTION 12. Ecological information ... / >>

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage \geq than 0,1%.

12.6. Endocrine disrupting properties

Based on the available data, the product does not contain substances listed in the main European lists of potential or suspected endocrine disruptors with environmental effects under evaluation.

12.7. Other adverse effects

Information not available

SECTION 13. Disposal considerations**13.1. Waste treatment methods**

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number or ID number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Not applicable

14.7. Maritime transport in bulk according to IMO instruments

Information not relevant

SECTION 16. Other information ... / >>**LEGEND:**

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- ATE: Acute Toxicity Estimate
- CAS: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE: Identifier in ESIS (European archive of existing substances)
- CLP: Regulation (EC) 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: Regulation (EC) 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA: Time-weighted average exposure limit
- TWA STEL: Short-term exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 2020/878 (II Annex of REACH Regulation)
4. Regulation (EC) 790/2009 (I Atp. CLP) of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
12. Regulation (EU) 2016/1179 (IX Atp. CLP)
13. Regulation (EU) 2017/776 (X Atp. CLP)
14. Regulation (EU) 2018/669 (XI Atp. CLP)
15. Regulation (EU) 2019/521 (XII Atp. CLP)
16. Delegated Regulation (UE) 2018/1480 (XIII Atp. CLP)
17. Regulation (EU) 2019/1148
18. Delegated Regulation (UE) 2020/217 (XIV Atp. CLP)
19. Delegated Regulation (UE) 2020/1182 (XV Atp. CLP)
20. Delegated Regulation (UE) 2021/643 (XVI Atp. CLP)
21. Delegated Regulation (UE) 2021/849 (XVII Atp. CLP)

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- IFA GESTIS website
- ECHA website
- Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

SECTION 16. Other information ... / >>

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

CALCULATION METHODS FOR CLASSIFICATION

Chemical and physical hazards: Product classification derives from criteria established by the CLP Regulation, Annex I, Part 2. The data for evaluation of chemical-physical properties are reported in section 9.

Health hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 3, unless determined otherwise in Section 11.

Environmental hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 4, unless determined otherwise in Section 12.

Changes to previous review:

The following sections were modified:

01 / 02 / 03 / 04 / 09 / 11 / 12 / 13 / 14 / 15 / 16.