

High-performance drill bit with indexable inserts Top Cut 4 drilling depth 5xD

WIDIA

Universal application up to 1300 N/mm² in the diameter range of 12.00–55.00 mm

Application:

High-performance drilling in the diameter range of 12.00 mm–55.00 mm and at drilling depths of 5xD for the steel, stainless steel, aluminium and cast iron material groups. With medium requirements for surface quality and tolerance



Execution:

- Four easily selectable cutting material types and four chip shape geometries for machining steel, stainless steel, aluminium, cast iron as well as superalloys and titanium

Advantage:

- Four true cutting edges per indexable insert for the entire range
- trouble-free application for cross-drilled holes, inclined inlet and outlet holes, chain holes, convex entry surfaces and drilling in half cylinder
- Internal and external indexable inserts are designed to prevent confusion

Art. no.	11212 165
Brand	WIDIA
Manufacturer Part Number	5577953
Suitable for min. cutting diameter	16.5 mm
Shank diameter	25 mm
Length	156.1 mm
Cantilever length	106.1 mm
Max. drilling depth (D)	5xD
Drill tip length	0.6 mm
Suitable for indexable inserts type	B
Projecting length	106.1 mm
Coolant supply	Internal
Shaft length	50 mm
Cutting direction	Right-hand cutting
Tool holding device	Parallel shank with chuck surface ISO 9766
Bore type	Normal bore, Stud hole bore, Bore from the center, Entry 45 ° edge, Half bore, Chain bore, Convex entry, L-Bore, Cross bore, Slanted exit, Slanted entry, T-Bore
Gross Weight	0.357 kg
Product Group	1XB

EAN

4050841100465

