

Modular drilling system TDMX drilling depth 5xD

For universal use up to 1300 N/mm², in diameter range of 16.00-40.00 mm

WIDIA 

Execution:

- Drilling depth 5xD
- Diameter range 16-38 mm

Advantage:

- Front clamping, possible to change the cutting body while clamped
- Up to 3x regrinding possible
- Polished chip grooves for better chip removal
- Types developed for material-specific applications



Art. no.	11228 230
Brand	WIDIA
Manufacturer Part Number	6572142
Suitable for min. cutting diameter	23 mm
Suitable for max. cutting diameter	23.99 mm
Shank diameter	25 mm
Length	217 mm
Cantilever length	161 mm
Effective length	120 mm
Shaft length	56 mm
Suitable for indexable inserts type	H
Max. drilling depth (D)	5xD
Coolant supply	Internal
Tool holding device	Parallel shank with chuck surface ISO 9766
Bore type	Normal bore, Stud hole bore, Cross bore, Slanted exit, Slanted entry
Gross Weight	0.510 kg
Product Group	1XB