

Combination workbench, series V 2800

Zinc sheet coating 2800 mm, 6 drawers with full extension



Execution:

- Solidly welded steel sheet construction
- Base with drawer block
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- Delivered fully assembled
- Per workstation 3 drawers with 100% full extension, 2 x front height 90 mm, 1 x front height 360 mm



Art. no.	50203 376
Brand	ANKE
Manufacturer Part Number	999.035.0127
Number of drawers	6 PCS
Working height	850 mm
Worktop width	2800 mm
Worktop height	50 mm
Pullout type	Full extension
Worktop depth	700 mm
Colour of front	Optional
Cabinet colour	Optional
Adjustable in height	No
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Surface	Powder-coated
Load-carrying capacity	800 kg
Drawer front height	4 x 90 mm, 2 x 360 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Material of worktop	Zinc sheet covering
Material of base frame	Steel plate
Drawer width (inner dimension)	500 mm
Drawer depth (inner dimension)	540 mm
Levelling	Yes
Load-carrying capacity per drawer	100 kg
Central locking	Yes
Gross Weight	225.180 kg
Product Group	502

EAN

4014641036690