



MICROMASTER 4 BRAKING RESISTOR 380-480 V 15R 44000 W
PK 2200 W CONT 301 X 326 X 484 MM H X W X D IP20

Figure similar

Order number	6SE6400-4BD22-2EA1
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Active power consumption / Rated value	2.2 kW
• maximum	44 kW
Type of electrical connection / for power cable	M6 screw studs
Design of the temperature switch	Normally closed contact
Input voltage / of the temperature switch / with AC / maximum	250 V
Input current / of the temperature switch / with AC / maximum	2.5 A
Protection class IP	IP20
Electrical resistance / of the braking resistor	15 Ω
Width	326 mm
Height	301 mm
Depth	484 mm
Net weight	11 kg

Further information

Information und Download Center

https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx

Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SE64004BD222EA1/all>

Industry Online Support

<http://support.automation.siemens.com/WW/view/en/6SE64004BD222EA1/all>