




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Strain Relief**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Strain Relief
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

Panel Mount Feature	With
---------------------	------

Dimensions

	1.455 in
--	----------

Operation/Application

For Use With	Interface Bus IDC Connectors, Shielded Panel Mount Connectors
--------------	---

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021
(211)

Does not contain REACH SVHC

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CHAMP Docking Connectors





IDC D-Sub Connectors(85)



PCB D-Sub Connectors(1)

Customers Also Bought

TE Part #0462-209-16141
DEUTSCH SOLID CONTACTSTE Part #W6P
DEUTSCH DT WEDGELOCKSTE Part #114017-ZZ
DEUTSCH SEALING PLUGSTE Part #1-480698-0
02P UMNL PLUG HSG NATLTE Part #1-2314786-1
LUMAWISE N ENHANCED BASE, FM
ON, ZC YESTE Part #2-2301994-3
RJ45 JACK INT.MAG. 1GB LED 1X1TE Part #2-1624116-6
BMB-A 0603 40R N8

Documents

Product Drawings

STRAIN RELIEF 24 POS BLACK

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-552298-1_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-552298-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-552298-1_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Instruction Sheets

Instruction Sheet (U.S.)

English