

## Electronic micrometer

MICROMASTER IP54 with data output



### Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

### Execution:

- Carbide measuring faces
- Advanced friction coupling for consistent, repeatable measuring force
- Zero setting at any position
- mm/inch switch-over
- Auto off
- Preset function
- ABS function
- Display blocking function

### Delivery:

In a case, with battery (1 x 3 V lithium, type CR 2032)



<b>Art. no.</b>	<b>31409 225</b>
<b>Brand</b>	TESA
<b>Manufacturer Part Number</b>	06030076
<b>Display</b>	Digital
<b>Min./max. length measuring range</b>	225-250 mm
<b>Min./max. length measuring range in inches</b>	9-10 in
<b>Digit increment</b>	0.001 mm
<b>Measuring surface diameter</b>	8 mm
<b>Material of measuring bolt</b>	Carbide
<b>IP protection class</b>	IP 54
<b>Data transmission type</b>	RS232 opto coupled
<b>Spindle clamping</b>	Yes
<b>Digit height</b>	7 mm
<b>Error limit</b>	8 µm
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Battery designation</b>	3V CR2032 Lithium
<b>DIN</b>	863
<b>Bracket depth</b>	140 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Calibration Group</b>	D
<b>Gross Weight</b>	2.000 kg
<b>Product Group</b>	362

### EAN

7630041116649