


IG6614



Inductive high-temperature sensor

IGA3005ZBPKG/5M/SH



Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range	[mm]	5
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 70

Application

Application	high-temperature applications
-------------	-------------------------------

Electrical data

Operating voltage	[V]	10...35 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes

Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Max. leakage current	[mA]	0.5
Permanent current rating of switching output DC	[mA]	150
Switching frequency DC	[Hz]	400
Short-circuit proof		yes
Overload protection		yes

Detection zone

Sensing range	[mm]	5
Operating distance	[mm]	0...4.1

Accuracy / deviations

Correction factor		stainless steel: 0.6 / brass: 0.3 / aluminium: 0.2 / copper: 0.1
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-15...15


IG6614



Inductive high-temperature sensor

IGA3005ZBPKG/5M/SH

Operating conditions		
Ambient temperature [°C]	0...180	
Protection	IP 65	
Tests / approvals		
EMC	EN 61000-4-2 ESD	2 kV CD / 4 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
MTTF [years]	185	
Mechanical data		
Weight [g]	263	
Housing	threaded type	
Mounting	flush mountable	
Dimensions [mm]	M18 x 1 / L = 70	
Thread designation	M18 x 1	
Materials	threaded sleeve: stainless steel; sensing face: LCP	
Accessories		
Accessories (supplied)	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 5 m, silicone, Ø 5 mm; highly flexible		
Connection		



Core colours :

- BK = black
- BN = brown
- BU = blue