

Franklin International

Safety Data Sheet

Titebond Original Wood Glue

Section 1. Identification

| | |
|--|--|
| GHS product identifier | : Titebond Original Wood Glue |
| Physical state | : Liquid. |
| Address | : Franklin International 2020 Bruck Street Columbus OH 43207 |
| Contact person | : Franklin Technical Services |
| Telephone | : (800) 877-4583 |
| In case of emergency | : Franklin Security (614) 445-1300 |
| e-mail address of person responsible for this SDS | : SDS@FranklinInternational.com |
| Reference number | : 2213 |
| Product code | : 5066 |
| Date of revision | : 4/24/2018 |
| Safety Data Sheets are available online at | : www.FranklinInternational.com |
| Chemtrec (24 Hour) | : (800) 424 - 9300 |
| Chemtrec International | : +1 703-741-5970 |
| Chemical family | : Adhesive. |

Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Industrial use wood glue.
Wide dispersive use of substances in professional and DIY adhesives.

Section 2. Hazards identification

| | |
|---|--|
| OSHA/HCS status | : While this material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200), this SDS contains valuable information critical to the safe handling and proper use of the product. This SDS should be retained and available for employees and other users of this product. |
| Classification of the substance or mixture | : Not classified. |
| GHS label elements | |
| Signal word | : No signal word. |
| Hazard statements | : No known significant effects or critical hazards. |
| Precautionary statements | |
| General | : Refer to safety data sheet before use. Avoid contact with skin and clothing. Wash thoroughly after handling. Get medical attention if needed. Contact Franklin International Technical Service for additional information at 1-800-877-4583. |
| Prevention | : Not applicable. |
| Response | : Not applicable. |

Section 2. Hazards identification

| | |
|---|-------------------|
| Storage | : Not applicable. |
| Disposal | : Not applicable. |
| Hazards not otherwise classified | : None known. |

Section 3. Composition/information on ingredients

Substance/mixture : Mixture

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

Description of necessary first aid measures

| | |
|---------------------|---|
| Eye contact | : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs. |
| Inhalation | : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if needed. |
| Skin contact | : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if needed. |
| Ingestion | : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if needed. |

Most important symptoms/effects, acute and delayed

Potential acute health effects

| | |
|---------------------|---|
| Eye contact | : This product may irritate eyes upon contact. |
| Inhalation | : No known significant effects or critical hazards. |
| Skin contact | : No known significant effects or critical hazards. |
| Ingestion | : No known significant effects or critical hazards. |

Over-exposure signs/symptoms

| | |
|---------------------|---------------------|
| Eye contact | : No specific data. |
| Inhalation | : No specific data. |
| Skin contact | : No specific data. |
| Ingestion | : No specific data. |

Indication of immediate medical attention and special treatment needed, if necessary

| | |
|-----------------------------------|---|
| Notes to physician | : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled. |
| Specific treatments | : No specific treatment. |
| Protection of first-aiders | : No action shall be taken involving any personal risk or without suitable training. |

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.
- Specific hazards arising from the chemical** : In a fire or if heated, a pressure increase will occur and the container may burst.
- Hazardous thermal decomposition products** : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide
- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Stop leak if without risk. Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

Section 7. Handling and storage

Conditions for safe storage, including any incompatibilities : Store between the following temperatures: 4.4444 to 32.222°C (40 to 90°F). Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

None.

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Eye/face protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

Skin protection

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Body protection : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Other skin protection : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

Section 9. Physical and chemical properties

Appearance

Physical state : Liquid.
Color : Yellow.
Odor : Faint odor.
Odor threshold : Not available.
pH : 3.8 to 4.7

Section 9. Physical and chemical properties

| | |
|---|-------------------------------|
| Melting point | : Not available. |
| Boiling point | : 98.889°C (210°F) |
| Flash point | : Closed cup: Not applicable. |
| Evaporation rate | : <1 (butyl acetate = 1) |
| Flammability (solid, gas) | : Not available. |
| Lower and upper explosive (flammable) limits | : Not available. |
| VOC (less water, less exempt solvents) | : 10.7 g/l |
| Volatility | : 54.1% (w/w) |
| Vapor density | : Not available. |
| Relative density | : 1.0771 |
| Solubility | : Not available. |
| Solubility in water | : Not available. |
| Partition coefficient: n-octanol/water | : Not available. |
| Auto-ignition temperature | : Not available. |
| Decomposition temperature | : Not available. |
| Viscosity | : Not available. |

Section 10. Stability and reactivity

| | |
|---|--|
| Reactivity | : No specific test data related to reactivity available for this product or its ingredients. |
| Chemical stability | : The product is stable. |
| Possibility of hazardous reactions | : Under normal conditions of storage and use, hazardous reactions will not occur. |
| Conditions to avoid | : No specific data. |
| Incompatible materials | : No specific data. |
| Hazardous decomposition products | : Under normal conditions of storage and use, hazardous decomposition products should not be produced. |

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Not available.

Irritation/Corrosion

Not available.

Conclusion/Summary

| | |
|--------------------|--|
| Skin | : Prolonged or repeated contact can defat the skin and lead to irritation, cracking and/or dermatitis. |
| Eyes | : This product may irritate eyes upon contact. |
| Respiratory | : Inhalation of oil mist or vapors at elevated temperatures may cause respiratory irritation. |

Sensitization

Not available.

Mutagenicity

Not available.

Section 11. Toxicological information

Carcinogenicity

Not available.

Reproductive toxicity

Not available.

Teratogenicity

Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Information on the likely routes of exposure : Routes of entry anticipated: Oral, Inhalation.
Routes of entry not anticipated: Dermal.

Potential acute health effects

Eye contact : This product may irritate eyes upon contact.
Inhalation : No known significant effects or critical hazards.
Skin contact : No known significant effects or critical hazards.
Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact : No specific data.
Inhalation : No specific data.
Skin contact : No specific data.
Ingestion : No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects : Not available.
Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.
Potential delayed effects : Not available.

Potential chronic health effects

Not available.

General : No known significant effects or critical hazards.
Carcinogenicity : No known significant effects or critical hazards.
Mutagenicity : No known significant effects or critical hazards.
Teratogenicity : No known significant effects or critical hazards.
Developmental effects : No known significant effects or critical hazards.
Fertility effects : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Not available.

Section 12. Ecological information

Toxicity

Not available.

Persistence and degradability

Not available.

Bioaccumulative potential

Not available.

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Section 14. Transport information

| | DOT Classification | TDG Classification | Mexico Classification | ADR/RID | IMDG | IATA |
|-----------------------------------|-------------------------------|-------------------------------|----------------------------------|----------------|----------------|----------------|
| UN number | Not regulated. | Not regulated. | Not regulated. | Not regulated. | Not regulated. | Not regulated. |
| UN proper shipping name | - | - | - | - | - | - |
| Transport hazard class(es) | - | - | - | - | - | - |
| Packing group | - | - | - | - | - | - |
| Environmental hazards | No. | No. | No. | No. | No. | No. |

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Section 15. Regulatory information

U.S. Federal regulations

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : Not applicable.

Composition/information on ingredients

No products were found.

State regulations

Massachusetts : None of the components are listed.

New York : None of the components are listed.

New Jersey : None of the components are listed.

Pennsylvania : None of the components are listed.

California Prop. 65

None of the components are listed.

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

Inventory list

China : Not determined.

United States TSCA 8(b) inventory : All components are listed or exempted.

Section 16. Other information

Hazardous Material Information System (U.S.A.)

| | | |
|------------------|---|---|
| Health | / | 0 |
| Flammability | | 0 |
| Physical hazards | | 0 |
| | | |

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings and the associated label are not required on SDSs or products leaving a facility under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered trademark and service mark of the American Coatings Association, Inc.

Section 16. Other information

The customer is responsible for determining the PPE code for this material. For more information on HMIS® Personal Protective Equipment (PPE) codes, consult the HMIS® Implementation Manual.

[National Fire Protection Association \(U.S.A.\)](#)



Reprinted with permission from NFPA 704-2001, Identification of the Hazards of Materials for Emergency Response Copyright ©1997, National Fire Protection Association, Quincy, MA 02269. This reprinted material is not the complete and official position of the National Fire Protection Association, on the referenced subject which is represented only by the standard in its entirety.

Copyright ©2001, National Fire Protection Association, Quincy, MA 02269. This warning system is intended to be interpreted and applied only by properly trained individuals to identify fire, health and reactivity hazards of chemicals. The user is referred to certain limited number of chemicals with recommended classifications in NFPA 49 and NFPA 325, which would be used as a guideline only. Whether the chemicals are classified by NFPA or not, anyone using the 704 systems to classify chemicals does so at their own risk.

[Procedure used to derive the classification](#)

| Classification | Justification |
|-----------------|---------------|
| Not classified. | |

[History](#)

Date of printing : 12/18/2019

Date of issue/Date of revision : 4/24/2018

Date of previous issue : 4/24/2018

Version : 1

[Key to abbreviations](#)

: ATE = Acute Toxicity Estimate
 BCF = Bioconcentration Factor
 GHS = Globally Harmonized System of Classification and Labelling of Chemicals
 IATA = International Air Transport Association
 IBC = Intermediate Bulk Container
 IMDG = International Maritime Dangerous Goods
 LogPow = logarithm of the octanol/water partition coefficient
 MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
 UN = United Nations

References : Not available.

☑ Indicates information that has changed from previously issued version.

[Notice to reader](#)

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.