



Figure similar

POWER SUPPLY; PHASES:1; PN(KW):0,24;
 UPRI(V):400-230+/-15; USEC(V DC):24; ISEC(A DC):10/12 (60/40 CEL); F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I;
 TA/ISOKL:60 /B; W(%):5; IP00; TYPE OF TERMINALS:SCREW/TAB CONNECTION;
 INSTALLATION:SCREW; EN 61558-2-6, EN61131-2
 >SAFETY ISOLATING TRANSFORMER<

General technical data:

Product designation		4AV2400-2EB00-0A
product brand name		SIDAC
Vector group		II0
Certificate of suitability		CE
Product function		
<ul style="list-style-type: none"> • Temperature monitoring 		No
<ul style="list-style-type: none"> • Insulation monitoring 		No
<ul style="list-style-type: none"> • Short-circuit and overload proof 		No
<ul style="list-style-type: none"> • varistor protective wiring 		Yes
Operating resource protection class		I
Number of shielding windings		0

Inputs:

Phase number of the inputs		1
Type of current of the inputs		AC
Input voltage		
<ul style="list-style-type: none"> • _1 Rated value 	V	415
<ul style="list-style-type: none"> • _2 Rated value 	V	400
<ul style="list-style-type: none"> • _3 Rated value 	V	385
<ul style="list-style-type: none"> • _4 Rated value 	V	245
<ul style="list-style-type: none"> • _5 Rated value 	V	230
<ul style="list-style-type: none"> • _6 Rated value 	V	215
Electrical input frequency		
<ul style="list-style-type: none"> • minimum 	Hz	50

<ul style="list-style-type: none"> • maximum 	Hz	60
Input voltage		
<ul style="list-style-type: none"> • minimum 	V	193.5
<ul style="list-style-type: none"> • maximum 	V	439.9
Input current		
<ul style="list-style-type: none"> • _1 Rated value 	A	0.85
<ul style="list-style-type: none"> • _2 Rated value 	A	0.89
<ul style="list-style-type: none"> • _3 Rated value 	A	0.92
<ul style="list-style-type: none"> • _4 Rated value 	A	1.46
<ul style="list-style-type: none"> • _5 Rated value 	A	1.54
<ul style="list-style-type: none"> • _6 Rated value 	A	1.65
Type of electrical connection at input for main current circuit		screw-type terminals / tab terminals

Outputs:		
Type of current		DC
<ul style="list-style-type: none"> • _1 at output 		
Output voltage		
<ul style="list-style-type: none"> • _1 Rated value 	V	24
Output voltage of the measurement signal at analog output for DC maximum	V	28.8
Output voltage of the measurement signal at analog output for DC minimum	V	20.4
Output current		
<ul style="list-style-type: none"> • _1 Rated value 	A	10
Type of electrical connection at output for main current circuit		screw-type terminals / tab terminals
Relative residual ripple		
<ul style="list-style-type: none"> • of the output voltage 1 for main current circuit maximum 	%	5

Ambient conditions:		
Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	60
Protection class IP		IP00

Mechanical data:		
Mounting type		screws
Construction form of the iron core		EI 120/72
Width	m	120
Height	m	170
Depth	m	128

Certificates/ approvals:



[Declaration of
Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AV24002EB000A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AV24002EB000A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4AV24002EB000A&lang=en

last modified:

16.03.2015