

BLOC BRIDE clamping unit



Application:

For use on machine tools for drilling, milling, thread cutting and countersinking.

Execution:

- Stepless and simple adjustment of clamping height
- Clamping force infinitely variable up to 16 kN depending on stability and machining of workpiece (distortion-free clamping).
- Simultaneous clamping of the workpiece and fixing of the clamping unit to any point on the table by turning the spanner.
- Adjusts to shape of workpiece surface using interchangeable function shoes.
- Base elements without spanner

Advantage:

- Exchangeable T-shaped sliding blocks with compression spring for each groove width for fast assembly of the clamping unit.
- Interchangeable lever arms, short and long version, for good access to workpiece.



Art. no.	26245 010
Brand	KOPAL
Manufacturer Part Number	05 021
Max. left arm depth	33 mm
Max. right arm depth	77 mm
Min./max. clamping height	0-80 mm
Gross Weight	1.286 kg
Product Group	265